






REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE
-----	-----	-------------	------	------




SECTION A-A

3	DG129-Cage	X000000200(H)	XX	Brass	Ni plated
2	DG129-5.0-Cover	4029C0YXXA(H)	1	PA66	UL94V-0
1	DG129-5.0-Housing	4029A0YXXA(H)	1	PA66	UL94V-0
ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES

- NOTES:
- 1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
 - 2.PITCH: 5.00MM
 - 3.RATED VOLTAGE/CURRENT:UL 300V/20A
VDE 250V/20A
 - 4.OPERATION TEMPERATURES:-40℃~+105℃
 - 5.WITHSTANDING VOLTAGE:AC2000V/1MIN
 - 6.INSULATION RESISTANCE:5000MΩ/DC1000V
 - 7.WIRE RANGE: 26~12AWG,2.5MM²
 - 8.MAX.TORQUE VALUE:M3, 5.10KGF.CM
 - 9.UNDIMENSIONED TOLERANCES:

Pitch range in mm			Nominal dimension range in mm					
to 6	over 6 to 10	over 10 to 24	to 30	over 30 to 60	over 60 to 100	over 100 to 150	over 150	
±0.10	±0.15	±0.25	±0.2	±0.3	±0.5	±0.7	±1.0	0.05/10

5	DG129-Pin header	4029B00010(H)	XX	Barss	SnCe plated
4	DG129-Screws-M3	S000001430(H)	XX	Steel	Cr ³⁺ Zn

DETACHED LISTS	MM (INCH)		MATERIAL:		 DEGSON®					
	TOLERANCES EXCEPT AS NOTED		FINISH:							
	.X ± .XX ± .XXX ±		.X' ± .XX' ± .XXX' ±		PART NO.:		NAME: DG129-5.0-XXP-1Y-00A(H)			
	ANGLES ± 1°		APPD:		TITLE: ASSEMBLY DRAWING		REV	T8		
			CHKD:		DRAWING NO.: DG129-5.0-E02					
	THIRD ANGLE PROJECTION		DRFT: LIUM 09/09/05"		DO NOT SCALE DRAWING		SCALE	N/A	SHEET	1/1