



EV busbars 4Ph., 8HP, 63A for PLS. CLS. PKN., PFIM, PFHM, PFNM



**Part no.** EVG-4PHAS/8MODUL  
**Catalog No.** 215644

**EL-Nummer (Norway)** 1657147

Similar to illustration

## Delivery program

Basic function		Busbar
Basic function accessories		Busbar for miniature circuit-breaker Busbar for residual-current circuit-breakers Busbar for combined residual-current/power circuit-breaker
Busbar type		4-phase
Product range		EVG

## Technical data ETIM 7.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Phase busbar (ecI@ss10.0.1-27-37-13-06 [ACN992011])			
Number of phases			4
Number of poles			4
Suitable for number of devices			2
Pitch dimensions		mm	0
Cross section		mm <sup>2</sup>	10
Length		mm	142
Number of modular spacings			8
Rated permanent current I <sub>u</sub>		A	63
Type of electric connection			Fork
Insulated			Yes
Rated surge voltage		kV	4
Conditioned rated short-circuit current I <sub>q</sub>		kA	25
Max. rated operation voltage U <sub>e</sub>		V	500
Rated short-time withstand current I <sub>cw</sub>		kA	0
Suitable for devices with N-busbar			Yes
Suitable for devices with auxiliary switch			No