



Phase busbar, 1-phase, 10qmm, fork connector, 12SU

Part no. EVG-1PHAS/12MODUL
Catalog No. 215637

Similar to illustration

Delivery program

Basic function			Busbar
Basic function accessories			Busbar for miniature circuit-breaker Busbar for residual-current circuit-breakers Busbar for combined residual-current/power circuit-breaker
Busbar type			Single phase
Product range			EVG

Technical data ETIM 7.0

Low-voltage industrial components (EG000017) / Phase busbar (EC000215)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Phase busbar (ecI@ss10.0.1-27-37-13-06 [ACN992011])			
Number of phases			1
Number of poles			1
Suitable for number of devices			12
Pitch dimensions		mm	0
Cross section		mm ²	10
Length		mm	210
Number of modular spacings			12
Rated permanent current I _u		A	63
Type of electric connection			Fork
Insulated			Yes
Rated surge voltage		kV	4
Conditioned rated short-circuit current I _q		kA	25
Max. rated operation voltage U _e		V	500
Rated short-time withstand current I _{cw}		kA	0
Suitable for devices with N-busbar			No
Suitable for devices with auxiliary switch			No