

Female Header Pitch 2.0 mm angled

Double row, Height 6.35 mm



SPECIFICATION:

Current rating: 2 A
Insulation resistance: 1000 MΩ min.
Contact resistance: 20 mΩ max.
Dielectric voltage: 500 V AC
Operation temperature: -40 °C to +105 °C

MATERIAL:

Housing: Nylon 6T UL94V-0
Contacts: Copper alloy






HANDLING:

Processing: Wave soldering
Packing: Tube

TOLERANCE:

.X ± 0.25
.XX ± 0.20

RoHS
COMPLIANT



Recommended PCB Layout
(PCB Tolerance ±0.05)

Order-Information

Identifier:	No. of contacts:	Contact Plating:
FHR63D	#	#
Female Header Pitch 2.0 mm double row Height 6.35 mm	6: 2 x 3	G: Gold Flash *
	8: 2 x 4	S: Selective
	10: 2 x 5	
	:	
	80: 2 x 40	

* = standard