



**Double actuator pushbutton, RMQ-Titan, Pushbutton actuator I and indicator light flush, pushbutton actuator 0 non-flush, momentary, White lens, green, red, inscribed, Bezel: titanium**




**Part no. M22-DDLM-GR-X1/X0**  
**Catalog No. 284830**  
**Alternate Catalog No. M22-DDLM-GR-X1-X0Q**

## Delivery program

|                            |   |    |                                                                                            |
|----------------------------|---|----|--------------------------------------------------------------------------------------------|
| Product range              |   |    | RMQ-Titan                                                                                  |
| Basic function             |   |    | Double actuators                                                                           |
| Mounting hole diameter     | Ø | mm | 22.5                                                                                       |
| Single unit/Complete unit  |   |    | Single unit                                                                                |
| Design                     |   |    | Pushbutton actuator I and indicator light flush, pushbutton actuator 0 non-flush momentary |
| Description                |   |    | White lens                                                                                 |
| <b>Button plate</b>        |   |    |                                                                                            |
| button plate               |   |    | green, red                                                                                 |
| Button plate               |   |    |                                                                                            |
|                            |   |    | inscribed                                                                                  |
| Degree of Protection       |   |    | IP66                                                                                       |
| Front ring                 |   |    | Bezel: titanium                                                                            |
| Connection to SmartWire-DT |   |    | yes with SWD-RMQ connections                                                               |

## Technical data

|                             |              |                   |                                                                                |
|-----------------------------|--------------|-------------------|--------------------------------------------------------------------------------|
| <b>General</b>              |              |                   |                                                                                |
| Standards                   |              |                   | IEC/EN 60947<br>VDE 0660                                                       |
| Lifespan, mechanical        | Operations   | x 10 <sup>6</sup> | > 0.2                                                                          |
| Operating frequency         | Operations/h |                   | ≤ 3600                                                                         |
| Actuating force             |              | n                 | ≤ 5                                                                            |
| Climatic proofing           |              |                   | Damp heat, constant, to IEC 60068-2-78<br>Damp heat, cyclic, to IEC 60068-2-30 |
| Degree of Protection        |              |                   | IP66                                                                           |
| Ambient temperature         |              |                   |                                                                                |
| Open                        |              | °C                | -25 - +70                                                                      |
| Storage                     |              | °C                | - 40 - + 80                                                                    |
| Mounting position           |              |                   | As required                                                                    |
| Mechanical shock resistance |              | g                 | 30<br>Shock duration 11 ms<br>Sinusoidal according to IEC 60068-2-27           |
| shipping classification     |              |                   | DNV<br>GL<br>LR                                                                |



DNV



Germanischer Lloyd



Indoor and protected outdoor installation

## Design verification as per IEC/EN 61439

|                                                                                                                        |            |    |                                                                                                          |
|------------------------------------------------------------------------------------------------------------------------|------------|----|----------------------------------------------------------------------------------------------------------|
| Technical data for design verification                                                                                 |            |    |                                                                                                          |
| Rated operational current for specified heat dissipation                                                               | $I_n$      | A  | 0                                                                                                        |
| Heat dissipation per pole, current-dependent                                                                           | $P_{vid}$  | W  | 0                                                                                                        |
| Equipment heat dissipation, current-dependent                                                                          | $P_{vid}$  | W  | 0                                                                                                        |
| Static heat dissipation, non-current-dependent                                                                         | $P_{vs}$   | W  | 0                                                                                                        |
| Heat dissipation capacity                                                                                              | $P_{diss}$ | W  | 0                                                                                                        |
| Operating ambient temperature min.                                                                                     |            | °C | -25                                                                                                      |
| Operating ambient temperature max.                                                                                     |            | °C | 70                                                                                                       |
| IEC/EN 61439 design verification                                                                                       |            |    |                                                                                                          |
| 10.2 Strength of materials and parts                                                                                   |            |    |                                                                                                          |
| 10.2.2 Corrosion resistance                                                                                            |            |    | Meets the product standard's requirements.                                                               |
| 10.2.3.1 Verification of thermal stability of enclosures                                                               |            |    | Meets the product standard's requirements.                                                               |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat                                             |            |    | Meets the product standard's requirements.                                                               |
| 10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects |            |    | Meets the product standard's requirements.                                                               |
| 10.2.4 Resistance to ultra-violet (UV) radiation                                                                       |            |    | Please enquire                                                                                           |
| 10.2.5 Lifting                                                                                                         |            |    | Does not apply, since the entire switchgear needs to be evaluated.                                       |
| 10.2.6 Mechanical impact                                                                                               |            |    | Does not apply, since the entire switchgear needs to be evaluated.                                       |
| 10.2.7 Inscriptions                                                                                                    |            |    | Meets the product standard's requirements.                                                               |
| 10.3 Degree of protection of ASSEMBLIES                                                                                |            |    | Does not apply, since the entire switchgear needs to be evaluated.                                       |
| 10.4 Clearances and creepage distances                                                                                 |            |    | Meets the product standard's requirements.                                                               |
| 10.5 Protection against electric shock                                                                                 |            |    | Does not apply, since the entire switchgear needs to be evaluated.                                       |
| 10.6 Incorporation of switching devices and components                                                                 |            |    | Does not apply, since the entire switchgear needs to be evaluated.                                       |
| 10.7 Internal electrical circuits and connections                                                                      |            |    | Is the panel builder's responsibility.                                                                   |
| 10.8 Connections for external conductors                                                                               |            |    | Is the panel builder's responsibility.                                                                   |
| 10.9 Insulation properties                                                                                             |            |    |                                                                                                          |
| 10.9.2 Power-frequency electric strength                                                                               |            |    | Is the panel builder's responsibility.                                                                   |
| 10.9.3 Impulse withstand voltage                                                                                       |            |    | Is the panel builder's responsibility.                                                                   |
| 10.9.4 Testing of enclosures made of insulating material                                                               |            |    | Is the panel builder's responsibility.                                                                   |
| 10.10 Temperature rise                                                                                                 |            |    | Not applicable.                                                                                          |
| 10.11 Short-circuit rating                                                                                             |            |    | Is the panel builder's responsibility. The specifications for the switchgear must be observed.           |
| 10.12 Electromagnetic compatibility                                                                                    |            |    | Is the panel builder's responsibility. The specifications for the switchgear must be observed.           |
| 10.13 Mechanical function                                                                                              |            |    | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed. |

## Technical data ETIM 7.0

Low-voltage industrial components (EG000017) / Front element for push button (EC000221)

Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Front element for push-button actuators  
(ecI@ss10.0.1-27-37-12-10 [AKF028014])

|                             |  |    |       |
|-----------------------------|--|----|-------|
| Colour button               |  |    | Other |
| Number of command positions |  |    | 2     |
| Construction type lens      |  |    | Round |
| Hole diameter               |  | mm | 22.5  |
| Width opening               |  | mm | 0     |

|                                         |  |    |         |
|-----------------------------------------|--|----|---------|
| Height opening                          |  | mm | 0       |
| Type of button                          |  |    | Flat    |
| Suitable for illumination               |  |    | Yes     |
| With protective cover                   |  |    | No      |
| Labelled                                |  |    | Yes     |
| Switching function latching             |  |    | No      |
| Spring-return                           |  |    | Yes     |
| With front ring                         |  |    | Yes     |
| Material front ring                     |  |    | Plastic |
| Colour front ring                       |  |    | Chrome  |
| Degree of protection (IP), front side   |  |    | IP66    |
| Degree of protection (NEMA), front side |  |    | 4X      |

### Approvals

|                             |  |  |                                                                              |
|-----------------------------|--|--|------------------------------------------------------------------------------|
| Product Standards           |  |  | IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CSA-C22.2 No. 94-91; CE marking |
| North America Certification |  |  | Request filed for UL and CSA                                                 |
| Degree of Protection        |  |  | UL/CSA Type 3R, 4X, 12, 13                                                   |

### Dimensions

