



## TECHNICAL SPECIFICATIONS

**D-Sub Hood:**

|                        |                            |
|------------------------|----------------------------|
| Material:              | UL 94 V-0 Plastic Material |
| Plating:               | Nickel over Copper         |
| Operating Temperature: | -55°C to +110°C            |
| Cable Entry:           | Top Entry                  |
| Thumbscrews:           | UNC 4-40 (Standard)        |
| Cable O.D.:            | Up to 11,5mm               |

**Female D-Sub Solder Cup:**

|                        |                            |
|------------------------|----------------------------|
| Insulator:             | PBT, Black, UL94 V-0       |
| Shell:                 | Steel, Tin Plated          |
| Contact pins:          | Copper Alloy               |
| Stamped & Formed Pins  | Class 3, 100 inserts min.  |
| Machined Contact Pins: | Class 1, 500 inserts min.  |
| Contact Plating:       | Selective Gold over Nickel |
| Operating Temperature: | -55°C to +105°C            |
| Withstanding voltage:  | 1000V for 1 minute         |
| Insulator resistance:  | 1000MΩ min.                |

**Features:**

- Available in sizes 9-15-25-37
- Suitable for any common Sub-D Connector
- Strain relief inserts ensure a secure termination
- Re-openable
- Recyclable

| Size DTPK-M | Dim A | Dim B | Dim C |
|-------------|-------|-------|-------|
| 9-way       | 31,2  | 39,9  | 15,0  |
| 15-way      | 39,5  | 41,5  | 15,0  |
| 25-way      | 53,4  | 48,6  | 15,0  |
| 37-way      | 69,7  | 53,6  | 15,0  |

**Ordering information - Black Insulator:**

| Size:  | P/N - Kitted: | Class 3 - 100 inserts min. |
|--------|---------------|----------------------------|
| 9-way  | 6355-0030-11  | DTPK-M-09-DBS-K            |
| 15-way | 6355-0030-12  | DTPK-M-15-DBS-K            |
| 25-way | 6355-0030-13  | DTPK-M-25-DBS-K            |
| 37-way | 6355-0030-14  | DTPK-M-37-DBS-K            |

| Size:  | P/N - Kitted: | Class 1 - 500 inserts min. |
|--------|---------------|----------------------------|
| 9-way  | 6355-0031-11  | DTPK-M-09-DMS-K            |
| 15-way | 6355-0031-12  | DTPK-M-15-DMS-K            |
| 25-way | 6355-0031-13  | DTPK-M-25-DMS-K            |
| 37-way | 6355-0031-14  | DTPK-M-37-DMS-K            |

**Ordering information - White Insulator:**

| Size:  | P/N - Kitted: | Class 3 - 100 inserts min. |
|--------|---------------|----------------------------|
| 9-way  | 6355-8030-11  | DTPK-M-09-DBS-W-K          |
| 15-way | 6355-8030-12  | DTPK-M-15-DBS-W-K          |
| 25-way | 6355-8030-13  | DTPK-M-25-DBS-W-K          |
| 37-way | 6355-8030-14  | DTPK-M-37-DBS-W-K          |

| Size:  | P/N - Kitted: | Class 1 - 500 inserts min. |
|--------|---------------|----------------------------|
| 9-way  | 6355-8031-11  | DTPK-M-09-DMS-W-K          |
| 15-way | 6355-8031-12  | DTPK-M-15-DMS-W-K          |
| 25-way | 6355-8031-13  | DTPK-M-25-DMS-W-K          |
| 37-way | 6355-8031-14  | DTPK-M-37-DMS-W-K          |

