



PRODUCT NUMBER 65039-YXX(E)LF

DESIGN CODE
0 = STANDARD
2 = OPTIONAL RIB
SEE SHEET 2

INDICATES THE PRODUCT IS RoHS
COMPLIANT, SEE NOTE 6


65039-YXXLF OR 65039-YXXELF ARE
EXACTLY THE SAME PRODUCTS.
EXTENSION "E" JUST FOR OLD EUROPEAN
DESIGN AND MANUFACTURING SITE

PIN STYLE
SEE SHEET 2



NOTES:

- MOLDING MATERIAL : MODIFIED POLYPHELYNENE
COLOR BLACK, UL 94 V0
- LATCH MUST WITHSTAND 18N MIN PULL OUT FORCE
- STANDARD PACKAGING IN POLYBAGS
- TERMINALS MUST BE CRIMPED PROPERLY FOR
SATISFACTORY LATCHING :
- FOR CRIMPING INSTRUCTIONS, SEE TA-75 AND TA-295
- FOR TERMINAL APPLICATION SEE TA-531.
PRODUCT SPECIFICATION: BUS-12-067.
- THIS HOUSING IS INTENDED FOR USE WITH
MINI PV TERMINAL WITH 22-36 GAUGE WIRE
- RoHS COMPLIANT PRODUCT SPECIFICATIONS :
- MEETS PACKAGING SPECS AS PER GS-14-920
- PRODUCT MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS
DESCRIBED IN GS-22-008.
- THE PRODUCT IS NOT INTENDED TO BE EXPOSED
TO A MANUFACTURING SOLDER PROCESS.




mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family BERCONN			
ltr ecn no dr date				tolerances unless otherwise specified						title			
BE V07-0483 HTB 07.07.24				angles	linear	.X ±0.3		 mm	MINI LATCH SR POLARIZED HSG 2.54mm				
BF F12-0064 LMU 12.06.08						.XX ±0.13							
BG B-14321 LMU 13.03.21						.XXX ±0.05							
BH B-18693 LMU 14.08.29				dr	L.MULIN	12.06.08			dwg no		sheet 1 of 2		size
BJ B-20324 AMA 15.02.27				enrg	L.MULIN	12.06.08			65039		A3		
				chr									
				appd	JCO	12.06.08							
sheet index		revision sheet		BJ 1	BH 2								



FCIconnect.com

Copyright FCI

PIN STYLE	No. OF POS.	DIM J	DIM K
36	1x01	N/A	2.39
35	1x02	2.54	4.93
34	1x03	5.08	7.47
33	1x04	7.62	10.01
32	1x05	10.16	12.55
31	1x06	12.70	15.09
30	1x07	15.24	17.63
29	1x08	17.78	20.17
28	1x09	20.32	22.71
27	1x10	22.86	25.25
26	1x11	25.40	27.79
25	1x12	27.94	30.33
24	1x13	30.48	32.87
23	1x14	33.02	35.41
22	1x15	35.56	37.95
21	1x16	38.10	40.49
20	1x17	40.64	43.03
19	1x18	43.18	45.57
18	1x19	45.72	48.11
17	1x20	48.26	50.65
16	1x21	50.80	53.19
15	1x22	53.34	55.73
14	1x23	55.88	58.27
13	1x24	58.42	60.81
12	1x25	60.96	63.35
11	1x26	63.50	65.89
10	1x27	66.04	68.43
09	1x28	68.58	70.97
08	1x29	71.12	73.51
07	1x30	73.66	76.05
06	1x31	76.20	78.59
05	1x32	78.74	81.13
04	1x33	81.28	83.67
03	1x34	83.82	86.21
02	1x35	86.36	88.75
01	1x36	88.90	91.29



mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family BERCONN
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title
BE	V07-0483	HTB	07.07.24	angles	.x ±0.3		MINI LATCH SR
BF	F12-0064	LMU	12.06.08	linear	.xx ±0.13		POLARIZED HSG 2.54mm
BG	B-18693	LMU	14.08.29		.xxx ±0.05	scale 5:1	
BH	B-20324	AMA	15.02.27	dr	L.MULIN 12.06.08		dwg no sheet 2 of size
				enr	L.MULIN 12.06.08		65039 A3
				chr			
				appd	JCO 12.06.08		type CUSTOMER Drawing
sheet index	revision sheet						