

## Board-to-Wire Connectors Pitch 3.96 mm Series CGM

Wafers for housing CGM single row,  
straight



### SPECIFICATION:






Operating Voltage (Max.):	250 V
Operating Current (Nom.):	5 A
Operating Temperature:	-25°C to 85°C
Insulation Resistance (Min.):	1000 MΩ
Contact Resistance (Max.):	10 mΩ
Dielectric Strength:	1,500 Vac

### MATERIAL:

Material (Terminal):	brass, tin plated
Material (Housing):	nylon 66
Flammability Class:	UL 94 V-2
Material (Contact Area):	brass, tin plated

### HANDLING:

Packaging:	bulk
------------	------



## Order Information

Identifier:

CGV

No. of Contacts:

#

Wafer series CGM pitch 3.96 mm single row straight

2: 1 x 2

3: 1 x 3

4: 1 x 4

:

20: 1 x 20