

HellermannTyton

Pennycross Close, Plymouth, Devon, PL2 3NX, England
Telephone: +44(0)1752 701261 Fax: +44(0)1752 790058

Product Safety Data Sheet

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND COMPANY/UNDERTAKING

PRODUCT NAME: H, TH, ZH, ZTH

Address/Phone No: Hellermann Tyton
Pennycross Close
Plymouth
Devon
PL2 3NX

(01752) 701261

2. COMPOSITION/INFORMATION ON INGREDIENTS

PRODUCT DESCRIPTION Polychloroprene Tubings & Sleeves

HAZARDOUS INGREDIENT(S)	CAS No.	%(w/w)	Symbol	R Phrases
None				

3. HAZARDOUS IDENTIFICATION

No associated hazards at normal working temperatures. Hazard warning not required.

4. FIRST-AID MEASURES

Inhalation: Not applicable at normal working temperatures.
Skin Contact: In case of prolonged contact wash skin with soap and water.
Eye Contact: Irrigate thoroughly with water or eyewash solution.
Ingestion: Not normally required.

PRODUCT NAME:

H, TH, ZH, ZTH

5. FIRE-FIGHTING MEASURES

Extinguishing Media: Dry Powder, Water Mist, Foam

Fire Fighting Protective Equipment: Self-contained breathing apparatus

6. ACCIDENTAL RELEASE MEASURES

Personal precautions: Not anticipated

Spill response: Place in suitable containers for re-cycling or disposal.

Methods of disposal: Authorised land fill

7. HANDLING AND STORAGE

7.1 HANDLING

Provide adequate ventilation.

Observe good industrial hygiene.

7.2 Storage

Store at room temperature in a dry, adequately ventilated area.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Not applicable

Occupational Exposure Limits

HAZARDOUS INGREDIENT(S)

**LTEL
ppm**

**TWA
mg/m3**

**STEL
ppm**

**Time
mins**

PRODUCT NAME:**H, TH, ZH, ZTH**

9. PHYSICAL AND CHEMICAL PROPERTIES

Form : Cross-linked synthetic rubber tubing.
Colour : Various
Odour : Slight
Odour Threshold (ppm) : N/A
Boiling Point (°C) : N/A
Melting Point (°C) : N/A
Flammable Limits : N/A
Auto Ignition Temperature (°C) : N/D
Density (g/ml) : 1.3 - 1.5
Solubility (Water) : Insoluble
Solubility (Other) : N/A
Decomposition Temperature (°C) : 200°C

Softening Point : N/A

10. STABILITY AND REACTIVITY

Hazardous Reactions : Stable unless overheated or combusted
Hazardous Decomposition Product(s) : HCl and CO₂

11. TOXICOLOGICAL INFORMATION

Inhalation : Not applicable at normal working temperatures
Skin Contact : Slight irritation may be observed after prolonged contact.
Eye Contact : Not Applicable
Ingestion : Do not ingest
Long Term Exposure : No effect on health observed

12. ECOLOGICAL INFORMATION**Persistence and Degradation**

Information on primary surfactant : No ecological effects known..

PRODUCT NAME:

H, TH, ZH, ZTH

13. DISPOSAL CONSIDERATIONS

Care should be taken to ensure compliance with EC, National and Local Regulations.

14. TRANSPORT INFORMATION

Not classified as hazardous for transport.

15. REGULATORY INFORMATION

These products do not normally present a danger to human health by inhalation or contact with the skin in the forms in which they are supplied. Such products do not require a label under Regulation 9 of CHIP2.

16. OTHER INFORMATION

This data sheet was prepared in accordance with Directive 9/155/EEC

Use: Cable Identification, protection and insulation

For other technical information, contact the address in Section 1.

Information in this publication is believed to be accurate and is given in good faith, but it is for the Customer to satisfy itself of the suitability for its own particular purpose. Accordingly, Hellermann Electric gives no warranty to the fitness of the Product for any particular purpose and any implied warranty or condition (statutory or otherwise) is excluded except to the extent that such exclusion is prevented by law. Freedom under Patent, Copyright and Designs cannot be assumed.
