



PRODUCT NUMBER	NO. OF POS	DIM K	DIM L	DIM C	DIM W DIM Z
78211-003LF	3	7.47	5.08	1.35	0.05
78211-004LF	4	10.01	7.62	1.35	0.05
78211-005LF	5	12.55	10.16	1.35	0.05
78211-006LF	6	15.09	12.70	1.35	0.10
78211-007LF	7	17.63	15.24	1.35	0.10
78211-008LF	8	20.17	17.78	1.35	0.10
78211-009LF	9	22.71	20.32	1.35	0.10
78211-010LF	10	25.25	22.86	1.35	0.10
78211-011LF	11	27.79	25.40	1.35	0.15
78211-012LF	12	30.33	27.94	1.35	0.15
78211-013LF	13	32.87	30.48	1.35	0.15
78211-014LF	14	35.81	33.02	1.35	0.15
78211-015LF	15	37.95	35.56	1.35	0.15
78211-103LF	3	7.47	5.08	2.54	0.05
78211-105LF	5	12.55	10.16	2.54	0.05
78211-106LF	6	15.09	12.70	2.54	0.10

- NOTES:
- MOLDING MATERIAL : MODIFIED POLYPHELYNENE
 COLOR BLACK, UL 94 V0
 - LATCH MUST WITHSTAND 18N MIN PULL OUT FORCE
 - STANDARD PACKAGING IN POLYBAGS
 - TERMINALS MUST BE CRIMPED PROPERLY FOR SATISFACTORY LATCHING :
 - FOR CRIMPING INSTRUCTIONS, SEE TA-75 AND TA-295
 - FOR TERMINAL APPLICATION SEE TA-531.
- PRODUCT SPECIFICATION: BUS-12-067.
- THIS HOUSING IS INTENDED FOR USE WITH MINI PV TERMINAL WITH 22-36 GAUGE WIRE
 - RoHs COMPLIANT PRODUCT SPECIFICATIONS :
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
 - THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.



mat'l. code 10036738				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family BERGCON													
ltr	ecn no	dr	date	tolerances unless otherwise specified				 mm scale 5:1		title MINI LATCH HOUSING SR POLARIZED													
K	V07-0533	HTB	07.08.21	angles	linear	.X ±0.3																	
L	B-14321	LMU	13.03.21			.XX ±0.13																	
						.XXX ±0.05				dwg no													
				dr	L.MULIN		13.03.21			sheet 1 of 1										size A3			
				engr	L.MULIN		13.03.21			78211													
				chr	J.COMPAGNON		13.03.21																
				appd	LMU		13.03.21																
sheet index		revision sheet																					