

circular Connector w. Harax M12 L4 M



Part number	21 03 212 1407
Specification	circular Connector w. Harax M12 L4 M
HARTING eCatalogue	https://b2b.harting.com/21032121407

Identification

Category	Connector
Series	Circular connectors M12
Identification	M12-L
Element	Cable connector
Specification	Straight

Version

Termination method	HARAX [®] connection technology
Gender	Male
Locking type	Screw locking
Number of contacts	4
Coding	A-coding

Technical characteristics

Conductor cross-section	0.34 ... 0.75 mm ²
Conductor cross-section	AWG 22 ... AWG 18
Wire outer diameter	≤2.6 mm
Rated current	6 A
Rated voltage	50 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Insulation resistance	≥10 ⁸ Ω
Contact resistance	≤10 mΩ
Ambient temperature	-40 ... +85 °C -5 ... +50 °C During connection
Tightening torque	0.6 Nm
Wrench size	A/F 17 Knurled screw / knurled nut
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 when mated



Pushing Performance

Technical characteristics

	IP67 when mated
Cable diameter	7 ... 8.8 mm
Overvoltage category	III
Isolation group	I ($600 \leq CTI$)

Material properties

Material (insert)	Polyamide
Material (contacts)	Brass
Surface (contacts)	Gold plated
Material (hood/housing)	Polyamide Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
----------	--

Commercial data

Packaging size	10
Net weight	37.1 g
Country of origin	Germany
Customs tariff number	85366990