Product information

Marine PWC Oil 10W-40

PI 25/06/05/2024



Description

High-performance motor oil based on synthetic technology. The special additive package ensures maximum engine performance and ideal wear protection. Guarantees the best possible lubrication, outstanding engine cleanliness and excellent friction values for wet clutches, even at high speeds. Satisfies or exceeds the requirements and specifications of the leading engine manufacturers.

Properties

- excellent wear resistance
- ensures maximum engine performance
- outstanding engine cleanliness
- optimum lubrication under all operating conditions
- tested for the use with catalytic converters
- especially suitable for wet clutches

Specifications

API SP • JASO MA2

LIQUI MOLY also recommends this product for vehicles or assemblies for which the following specifications or original part numbers are required

Honda • Kawasaki • SeaDoo • Suzuki • Yamaha

Technical data

SAE class (engine oils) 10W-40

SAE J300

Density at 15 °C 0,860 g/cm³

DIN 51757

Viscosity at 40 °C 96,0 mm²/s

ASTM D 7042-04

Viscosity at 100 °C 14.6 mm²/s

ASTM D 7042-04

Viscosity at -25 °C (CCS) <= 7000 mPas

ASTM D 5293

Viscosity index 158

DIN ISO 2909

Pour point -36 °C

DIN ISO 3016

Evaporation loss (Noack) 10,0 %

ASTM D 5800-08 Method

В

Flash point 238 °C

DIN ISO 2592

Total base number 7,0 mg KOH/g

DIN ISO 3771

Sulfate ash 0,8 g/100g

DIN 51575



Technical data

Color number (ASTM) L 2.0

DIN ISO 2049

Areas of application

Especially suitable for PWC (personal water craft) 4stroke engines. Ideal for sporting applications. Ideally suited for engines with or without a wet clutch.

Application

Note the engine or unit manufacturers' operating instructions.

Available pack sizes

1 l Canister plastic 25076

D-BOOKLET

4 l Canister plastic 25077

D-BOOKLET

Our information is based on thorough research and may be considered reliable, although not legally binding.