

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200878258

Status:

Active

Overview:

Brad Nano-Change (M8) Products

Description:

Nano-Change (M8) Double-Ended Cordset, 3 Poles, Female (Straight) to Male (Straight), 24 AWG, PVC Cable, 1.0m (3.28') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Cordsets
Series	120087
Connector End A	Nano-Change (M8)
Connector End B	Nano-Change (M8)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Protocol	N/A
Region	America
Type	Double Ended
UPC	78172554741
Physical	
Cable Diameter	5.00mm (.197")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Male
Keyway	None
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	145.000/g
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-25°C to +80°C
Wire Size AWG	24
Wire/Cable Type	UL 2464
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	60V
Material Info	
Engineering Number	443030E02M010
Reference - Drawing Numbers	
Sales Drawing	1200878240-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2020)9139-DC (19 Jan 2021)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120087 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION