





LAY OUT OF 50P CONNECTOR



WIRE WRAP CODE 4

ORDERING INFORMATION


SERIES	LEAD FREE
D B V 25 P 3 64 G T X XXX LF	SPECIAL CODES
SHELL SIZE E,A,B,C,D	DIMPLES
PANEL MOUNTING OPTIONS	X-ON MALE CONNECTORS ONLY
BLANK-STANDARD	SHELL PLATING
V-FEM. SCREW LOCK (UNC)	BLANK-ZINC (Cr+3)
N-FEM. SCREW LOCK M3	T-STD. TIN Over Cu
S-SPACER RIVETTED TO SHELL	PCB MOUNTING OPTIONS
L-CLINCH NUT (M3)	BLANK-STANDARD
O-CLINCH NUT (UNC)	G-HARPOON
NO.OF CONTACTS	CONTACT PLATING
09,15,25,37,50	64 - 200 MATING CYCLES
CONTACTS	65 - 500 MATING CYCLES
P - PIN	
S - SOCKET	
TERMINATION TYPE	
3-STRAIGHT SPILL	
4-WIRE WRAP	

"This LF product meets European Union Directives and other country regulations as described in GS-22-008"

The housing will withstand exposure to 260°C peak temperature for 3.5 seconds in a wave solder application with a 1.6mm minimum thick circuit board.


Packaging as per GS-14-920

EXTENDED FEMALE SCREW LOCK WITH SPACER




ORD CODE -8630-01-062

SPACERS RIVETTED TO SHELL




PREFIX:- S

MALE SCREW LOCK



ORD CODE:-
8630- 05(E.A.B.C.)
8630-03 D SHELL FEMALE
8630-15 D SHELL MALE
8630-04 E,A,B,C SHELL
WITH METAL HOOD
FOR 440 UNC 2A THREADED ADD UNC
TO THE CORRESPONDING ORD. CODE.

HARPOON PRESS FITTED TO SHELL

mat'l. code
SEE NOTE 4


ltr	ecn no	dr	date
D	I06-0074	GVJ	2006/06/08
E	I09-0179	AMR	2009/09/04
F	I09-0195	AMR	2009/09/04
G	I11-0003	AMR	2011/01/06
H	I11-0047	AMR	2011/03/05

sheet	revision	H
index	sheet	1


surface
ISO 1302 ✓ tolerance
ISO 406 ISO 1101

tolerances unless otherwise specified	projection	product family
angles	MM	title
linear	scale -	D- SUB S/S W/W CONNECTOR (WITH ASSEMBLY OPTIONS)
dr		dwg no
enr		sheet 1 of 1
chr		size
appd		A3


CLINCH NUT

L - M3
O - UNC4-40

HEXAGONAL FEMALE SCREW

N - M3
V - UNC4-40

HARPOON RIVETTED TO SHELL



50	P	66.65	52.68	61.11	11.08	14.99	11.09	5.85	55.07	13.31	1.50	1.0
	S	66.65	52.30	61.11	10.62	14.99	11.21	6.05	55.07	13.31	1.10	0.8
37	P	68.94	55.30	63.50	8.23	12.17	11.09	5.85	57.45	10.46	1.50	1.0
	S	68.94	54.71	63.50	7.77	12.17	11.21	6.05	57.45	10.46	1.10	0.8
25	P	52.65	38.84	47.04	8.23	12.17	11.07	5.85	41.02	10.46	1.10	0.8
	S	52.65	38.25	47.04	7.77	12.17	11.21	6.05	41.02	10.46	1.10	0.8
15	P	38.76	25.12	33.32	8.23	12.17	10.99	5.85	27.25	10.46	1.10	0.8
	S	38.76	24.54	33.32	7.77	12.17	11.21	6.05	27.25	10.46	1.10	0.8
09	P	30.43	16.79	24.99	8.23	12.17	10.99	5.85	19.02	10.46	1.10	0.8
	S	30.43	16.21	24.99	7.77	12.17	11.21	6.05	19.02	10.46	1.10	0.8
SHELL SIZE		A ^{+0.76} ₀	B ^{+0.25} ₀	C ^{±0.12}	D ^{+0.25} ₀	E ^{+0.76} ₀	F ^{MAX}	G ^{+0.15} ₀	H ^{+0.51} ₀	J ^{+0.51} ₀	K ^{±0.2}	L ^{+0.22} ₀

NOTE: INSIDE DIMENSION OF MALE AND OUTSIDE DIMENSION OF THE FEMALE CONNETOR

TECHNICAL SPECIFICATIONS

SHELLS	: TIN/ZINC PLATED STEEL
CONTACTS DIA ON ACTIVE AREA	: Ø1 MM.
CONTACTS MATERIAL	: COPPER ALLOY
CONTACT PLATING	: GXT / GOLD OVER NICKEL (ACTIVE ZONE) TIN OVER NICKEL (TERMINATION ZONE)
FOR LEAD FREE PLATING	: 2µ MIN. TIN TOP OVER 1.27µ MIN.NICKEL UNDER PLATE(ON TERMINATION ZONE)
INSULATOR MATERIAL	: SELF EXTINGUISHING THERMOPLASTIC- TO UL CLASS 94 V0 THE HOUSING WILL WITHSTAND EXPOSURE TO 260-265°C IF WE USE PROTECTIVE ADHESIVE (type Kapton or Teflon) OR PROTECTIVE METALLIC DEVICE
OPERATING TEMPERATURE	: -55°C +125°C
OPERATING CURRENT	: 5 A PER CONTACT
CONTACT RESISTANCE	: ≤10m Ω
INSULATION RESISTANCE	: ≥5000 M Ω
MAXIMUM VOLTAGE	: 1000 V.r.m.s
MECHANICAL ENDURANCE	: 500 MATINGS FOR CODE 64 200 MATINGS FOR CODE 65
DAMP HEAT	: 56 DAYS FOR ≥0.75µ GOLD PLATING 21 DAYS FOR ≤0.40µ GOLD PLATING