

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022012021](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 254 Crimp Housing, 2 Circuits, Natural

Documents:
[3D Model](#) [Packaging Specification 26950002-PK-000 \(PDF\)](#)
[3D Model \(PDF\)](#) [Test Summary TS-10-07-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-10-07-001 \(PDF\)](#)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	2695
Application	Signal, Wire-to-Board
Overview	KK Interconnect Solutions
Product Name	KK 254
UPC	800753594067
Physical	
Circuits (maximum)	2
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	0.241/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Stackable	No
Temperature Range - Operating	See Product Specification
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	2695-02
Reference - Drawing Numbers	
Packaging Specification	26950002-PK-000
Product Specification	PS-10-07-001
Sales Drawing	26950000-SD-000
Test Summary	TS-10-07-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2020)9139-DC (19
Jan 2021)
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
[2695](#) Series

Mates With
KK254 PCB Headers [42375](#) , [42377](#) , [42376](#)
 , [4030](#) , [6373](#) , [6410](#) , [171856](#) , [171857](#)

Use With
KK Crimp Terminals [2759](#) , [6459](#) , [41572](#)
 , [4809](#) , [8088](#)
 KK 254 Pre-Crimped
Leads [797580007](#) , [797580015](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION