



Manual Tensioning Tool with Plastic Housing

EVO7 up to 4.8 mm strap width

Features and Benefits

- Ergonomic, slip-proof handle for a comfortable and secure grip
- Extremely low maintenance
- Fast and precise application with minimum effort (TLC mechanism)
- Convenient and simple tension adjustment
- Extended, slim nose for use in narrow spaces
- Housing made of resilient and lightweight glass fibre-reinforced polyester
- Standard grip span (90 mm) and short grip span (80 mm) available



EVO7.

TYPE	Strap Width max.	Strap Thickness max.	Weight	Article-No.
EVO7	4.8	1.5	0.28 kg	110-70129
EVO7SP	4.8	1.5	0.28 kg	110-70130
BLADEKT	-	-	-	110-70106

All dimensions in mm. Subject to technical changes.

TLC-Technology: Tension – Lock – Cut

The new EVO7 protects muscles and joints and increases effectiveness

- Less recoil shock reduces impact to the operator's hand
- Application of force is significantly reduced



Application video: EVO7



1. Tension: Tie is tensioned as usual.

2. Lock: When the desired tension is met the locking mechanism locks the tie in place.



3. Cut: Innovative, effortless and less recoil shock cut-off function.



For product specific approvals and specifications please refer to the Appendix.