


Order code	Manufacturer code	Description
04-5828	n/a	TWIST TIE 4-7MM (PACK 100) (RC)
04-5830	n/a	TWIST TIE 7-10MM (PACK 100) (RC)
04-5832	n/a	TWIST TIE 10-13MM (PACK 100) (RC)
04-5834	n/a	TWIST TIE 13-16.5MM (PACK 100) (RC)
04-5836	n/a	TWIST TIE 16.5-20MM (PACK 100) (RC)
04-5838	n/a	TWIST TIE 20-26MM (PACK 100) (RC)


	Page 1 of 3
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003




1212 TWIST TIE



Material: UL approved Nylon 66, 94V-2 (Available in P.P. or P.E.)
 Colors available upon request.
 Tie-up cables at economical cost.
 Open the ties to feed cable and twist on to fix.



Standard design



TTU-08, -11, -15, -28

Unit:mm

Item No.	Dimension			Bundis Dimension	Packing
	A	B	C		
<input type="checkbox"/> TT-05	5.1	21.6	1.5	4.4	
<input type="checkbox"/> TT-08	7.0	25.0	2.0	7.0	
<input type="checkbox"/> TT-11	11.6	29.8	1.7	10.1	
<input type="checkbox"/> TT-15	15.0	33.8	1.9	13.4	
<input type="checkbox"/> TT-18	18.6	40.0	1.9	16.2	

<input type="checkbox"/> TT-24	23.6	45.0	2.0	21.3
<input type="checkbox"/> TTU-05	5.0	22.0	1.8	4.2
<input type="checkbox"/> TTU-08	8.1	26.2	2.3	7.2
<input type="checkbox"/> TTU-11	11.3	29.7	2.3	10.0
<input type="checkbox"/> TTU-15	14.8	32.6	2.0	13.2
<input type="checkbox"/> TTU-18	18.0	38.0	2.0	16.5
<input type="checkbox"/> TTU-22	22.0	42.3	2.0	19.8
<input type="checkbox"/> TTU-28	28.0	55.1	2.0	26.7

**100pcs
(1000pcs)**

