

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0003061121

Status:

Active

Overview:

Standard .062"+ and Standard .062" Pin and Socket Connector Systems

Description:

1.57mm Diameter Standard .062" Pin and Socket Receptacle Housing, 12 Circuits, with Standard Mounting Ears, Natural

Documents:

3D Model (PDF)

Drawing (PDF)

3D Model

Product Specification PS-02-06-001 (PDF)

Packaging Specification PK-1625-003-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	1625
Application	Power, Wire-to-Wire
Comments	Polarized to Mating Part
Overview	Standard .062"+ and Standard .062" Pin and Socket Connector Systems
Product Name	Standard .062"
UPC	800753753662
Physical	
Breakaway	No
Circuits (maximum)	12
Circuits Detail	3x4
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	3.080/g
Number of Rows	3
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	3.68mm
Pitch - Termination Interface	3.68mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Electrical	
Current - Maximum per Contact	5.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	1625-12R
Reference - Drawing Numbers	
Packaging Specification	PK-1625-003-001
Product Specification	PS-02-06-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Low-Halogen

Status

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Contained

RoHS Phthalates

Not Contained

Search Parts in this Series

1625 Series

Mates With

03062122

Use With

Female Crimp Terminals 1561 , 4559 , 4529 , 2190 , 2189 , 1787 , 1855 . Male Crimp Terminals 1560 , 1786 , 1854. 1778 Male PC Tail Terminals. 1779 Female PC Tail Terminals

This document was generated on 08/03/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION