

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	<u>0009503041</u>
Status:	Active
Overview:	KK® Interconnect System - Molex
Description:	KK 3.96mm Crimp Terminal Housing, Friction Ramp, 4 Circuits, Natural

Documents:

[3D Model](#)
[Product Specification PS-08-50-001 \(PDF\)](#)
[Drawing \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)
[3D Model \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	<u>2139</u>
Application	Power, Wire-to-Board
Overview	<u>KK® Interconnect System - Molex</u>
Product Name	KK 396
UPC	800753614024

Physical

Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.040/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Temperature Range - Operating	See Product Specification

Solder Process Data


Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number 2139-4A

Reference - Drawing Numbers

Product Specification	PS-08-50-001
Sales Drawing	SD-2139-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

2139 Series

Mates With

KK 396 Headers: 41771 , 41772 , 41791 ,
41792 , 42491 , 42492 , KK 396 Breakaway
Headers: 41661 , 41662 , 41671 , 41672

Use With

2478 Crimp Terminals for 18-24 AWG, 2578
Crimp Terminals for 22-26 AWG

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION