

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200868669](#)
Status: **Active**
Overview: Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Description: Nano-Change (M8) Single-Ended Cordset with Knurled Hexnut, 3 Poles, Female (90°) to Pigtail, 24 AWG, WSOR Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	120086
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Brass
Overview	<u>Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable</u>
Product Name	Nano-Change (M8)
Protocol	N/A
Region	Europe
Type	Single Ended
UPC	889056003742

Physical

Cable Diameter	4.50mm (.177")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	424.000/g
Orientation	90° to Pigtail
Poles	3
Temperature Range - Operating	-25°C to +85°C
Wire Size AWG	24
Wire/Cable Type	WSOR

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V

Material Info

Engineering Number	403001B41M050
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-120086-010-001
---------------	-------------------



Series image - Reference only

EU ELV

Compliant with Exemption 3

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Compliant with
Exemption 3

Not Contained

Search Parts in this Series

[120086](#) Series