

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192030388

Status:

Active

Overview:

High-Temperature Temp Terms Terminals and Splices

Description:

Krimptite Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 10 (M5)

Documents:

Drawing (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E32244

General

Product Family

Ring and Spade Terminals

Series

19203

Crimp Quality Equipment

Yes

Overview

High-Temperature Temp Terms Terminals and Splices

Product Name

Krimptite

Taxonomy

Ring and Spade Terminals

Type

Ring

UPC

822348424771

Physical

Barrel Type

Closed

Insulation

None

Material - Metal

Steel

Material - Plating Mating

Nickel

Net Weight

0.653/g

Packaging Type

Carton

Stud Size

10 (M5)

Temperature Range - Operating

483°C

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

4.19mm max.

Wire Size AWG

14, 16

Wire Size mm²

1.50-2.50

Material Info

Reference - Drawing Numbers

Product Specification

PS-19902-011-001, PS-19902-013-001

Sales Drawing

SD-19203-017-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2022)4187-DC (10

June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19203 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade	640030100
Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm²	
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION