

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022012097

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK 254 Crimp Housing, Friction Ramp, 9 Circuits, Natural

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-10-07-001 (PDF)

Packaging Specification 26950002-PK-000 (PDF)

Test Summary TS-10-07-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA	LR19980	
UL	E29179	
General		
Product Family	Crimp Housings	
Series	2695	
Application	Signal, Wire-to-Board	
Overview	KK Interconnect Solutions	
Product Name	KK 254	
UPC	800753689978	
Physical		
Circuits (maximum)	9	
Color - Resin	Natural (White)	
Flammability	94V-0	
Gender	Receptacle	
Glow-Wire Capable	No	
Lock to Mating Part	Yes	
Material - Resin	Nylon	
Net Weight	0.954/g	
Number of Rows	1	
Packaging Type	Bag	
Panel Mount	No	
Pitch - Mating Interface	2.54mm	
Pitch - Termination Interface	2.54mm	
Stackable	No	
Temperature Range - Operating	See Product Specification	
Solder Process Data		
Lead-freeProcess Capability	N/A	
Material Info		
Engineering Number	2695-09R	
Reference - Drawing Numbers		
Packaging Specification	26950002-PK-000	
Product Specification	PS-10-07-001	
Sales Drawing	26950000-SD-000	
Test Summary	TS-10-07-001	



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free
Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

2695 Series

Mates With

KK254 PCB Headers [42375](#) , [42377](#) , [42376](#)
, [4030](#) , [6373](#) , [6410](#) , [171856](#) , [171857](#)

Use With

KK Crimp Terminals [2759](#) , [6459](#) , [41572](#)
, [4809](#) , [8088](#)
 KK 254 Pre-Crimped
Leads [797580007](#) , [797580015](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION