

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022051022

Status:


Active

Overview:

Mini-Latch Wire-to-Board / Wire-to-Wire Connector System

Description:

Mini-Latch / KK Wire-to-Board Header, Right-Angle, with Friction Ramp, 2 Circuits, Tin (Sn) Plating, Natural



Series image - Reference only

Documents:	
3D Model	Application Specification 511910000-AS-000 (PDF)
3D Model (PDF)	Packaging Specification 50469200-SPK-200 (PDF)
Drawing (PDF)	Packaging Specification SPK-5046-001-001 (PDF)
Product Specification 50510002-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 511910000-PS-000 (PDF)	

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	5046
Application	Signal, Wire-to-Board
Overview	Mini-Latch Wire-to-Board / Wire-to-Wire Connector System
Product Name	KK, Mini-Latch
UPC	800753591417
Physical	
Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	234.200/mg
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.40mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

5046 Series

Mates With

2.50mm Pitch Housing 51191

Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V
Material Info	
Engineering Number	5046-02A
Reference - Drawing Numbers	
Application Specification	511910000-AS-000
Packaging Specification	50469200-SPK-200, SPK-5046-001-001
Product Specification	50510002-PS-000, 511910000-PS-000
Sales Drawing	50460002-000

This document was generated on 08/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION