

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026202081

Status:


Active

Overview:

KK Interconnect Systems

Description:

KK 396 Wire-to-Board Header, Vertical Round Pin, 8 Circuits, Tin (Sn) Plating, with Mating Pin Length of 11.43mm (.450")



Series image - Reference only

Documents:

- 3D Model

Packaging Specification PK-3192-001-001 (PDF)
- 3D Model (PDF)

Symbol Footprint Data SYM-26-20-2081-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-99020-0087-001 (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Component Type

Overview

Product Name

Taxonomy

UPC

PCB Headers

3192

Board-to-Board, Power, Wire-to-Board

PCB Header

KK Interconnect Systems

KK 396

PCB Headers and Receptacles

800753734982

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

No

8

8

Natural

25

No

94V-2

No

No

None

None

Brass

Tin

Tin

Nylon

1.946/g

1

Vertical

4.45mm

No

None

1.60mm

Bag

3.96mm

3.96mm

5.080µm

5.080µm

No

No

No

Yes

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

3192 Series

Mates With

3069 KK Crimp Terminal Housing, 3215 KK 396 PC Board Connector

Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	7.0A
Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Engineering Number	319208A
Reference - Drawing Numbers	
Packaging Specification	PK-3192-001-001
Product Specification	PS-99020-0087-001
Sales Drawing	SDAE-3192-NX-001
Symbol/Footprint Data	SYM-26-20-2081-001

This document was generated on 01/05/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION