

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [0026602020](#)  
**Status:** **Active**  
**Overview:** [KK Interconnect Solutions](#)  
**Description:** KK 396 Header, Vertical, without Peg, 2 Circuits, Tin (Sn) Plating

**Documents:**

|                                                          |                                                                |
|----------------------------------------------------------|----------------------------------------------------------------|
| <a href="#">3D Model</a>                                 | <a href="#">Packaging Specification 417710000-PK-000 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                            | <a href="#">Symbol Footprint Data SYM-26-60-2020 (PDF)</a>     |
| <a href="#">3D Model (PDF)</a>                           | <a href="#">RoHS Certificate of Compliance (PDF)</a>           |
| <a href="#">Product Specification PS-08-50-001 (PDF)</a> |                                                                |

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |                                           |
|----------------|-------------------------------------------|
| Product Family | PCB Headers                               |
| Series         | <a href="#">41771</a>                     |
| Application    | Board-to-Board, Power, Wire-to-Board      |
| Overview       | <a href="#">KK Interconnect Solutions</a> |
| Product Name   | KK 396                                    |
| UPC            | 800754396387                              |

**Physical**

|                                |                           |
|--------------------------------|---------------------------|
| Breakaway                      | No                        |
| Circuits (Loaded)              | 2                         |
| Circuits (maximum)             | 2                         |
| Color - Resin                  | Natural                   |
| Durability (mating cycles max) | 25                        |
| Flammability                   | 94V-0                     |
| Glow-Wire Capable              | No                        |
| Lock to Mating Part            | None                      |
| Material - Metal               | Brass                     |
| Material - Plating Mating      | Tin                       |
| Material - Plating Termination | Tin                       |
| Material - Resin               | Polyester                 |
| Net Weight                     | 0.546/g                   |
| Number of Rows                 | 1                         |
| Orientation                    | Vertical                  |
| PC Tail Length                 | 3.56mm                    |
| PCB Locator                    | No                        |
| PCB Retention                  | None                      |
| PCB Thickness - Recommended    | 1.60mm                    |
| Packaging Type                 | Bag                       |
| Pitch - Mating Interface       | 3.96mm                    |
| Plating min - Mating           | 5.080µm                   |
| Plating min - Termination      | 5.080µm                   |
| Polarized to Mating Part       | Yes                       |
| Polarized to PCB               | No                        |
| Shrouded                       | Partial                   |
| Stackable                      | Yes                       |
| Temperature Range - Operating  | See Product Specification |
| Termination Interface: Style   | Through Hole              |

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 7.0A |
| Voltage - Maximum             | 250V |



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**

[41771](#) Series

**Mates With**

[2139](#) KK Crimp Housing, [41695](#) KK Crimp Housing, [6442](#) KK Crimp Housing, [2145](#) PCB Connector, [41815](#) PCB Connector, [3069](#) KK Crimp Housing

**Solder Process Data**

|                                                |      |
|------------------------------------------------|------|
| Duration at Max. Process Temperature (seconds) | 005  |
| Lead-freeProcess Capability                    | WAVE |
| Max. Cycles at Max. Process Temperature        | 001  |
| Process Temperature max. C                     | 235  |

**Material Info**

|                    |            |
|--------------------|------------|
| Engineering Number | 41771-0002 |
|--------------------|------------|

**Reference - Drawing Numbers**

|                         |                                    |
|-------------------------|------------------------------------|
| Packaging Specification | 417710000-PK-000                   |
| Product Specification   | PS-08-50-001                       |
| Sales Drawing           | SD-41771-001-000, SD-41771-001-002 |
| Symbol/Footprint Data   | SYM-26-60-2020                     |

This document was generated on 07/29/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**