

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5013300400](#)
Status: **Active**
Overview: Pico-Clasp Wire-to-Board Connectors
Description: 1.00mm Pitch, Pico-Clasp Low-Halogen Receptacle Crimp Housing, Single Row, Friction Lock, 4 Circuits, White

Documents:

Drawing (PDF)	Product Specification 5013301000-PS-001 (PDF)
3D Model	Application Specification 5013300000-AS-000 (PDF)
3D Model (PDF)	Packaging Specification SPK-501330-001-001 (PDF)
Product Specification 5013300000-PS-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

Application tooling part link

Application Tooling Part Link 63813-1700

General

Product Family Crimp Housings
Series [501330](#)
Application Signal, Wire-to-Board
Overview [Pico-Clasp Wire-to-Board Connectors](#)
Product Name Pico-Clasp
UPC 822348528974

Physical

Circuits (maximum) 4
Color - Resin White
Gender Receptacle
Glow-Wire Capable No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 33.100/mg
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 1.00mm
Pitch - Termination Interface 1.00mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification 5013300000-AS-000
Packaging Specification SPK-501330-001-001
Product Specification 5013300000-PS-001, 5013301000-PS-001
Sales Drawing 5013300000-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[501330](#) Series

Mates With

Pico-Clasp Vertical Header [501331](#) , [504449](#)
, [203556](#) , [203557](#) . Pico-Clasp Right-Angle
Header [501568](#) , [202396](#) , [203558](#) , [203559](#)

Use With

Pico-Clasp Female Terminal [501334](#) (Tin),
[501193](#) (Gold)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for [638131700](#)
Pico-Clasp Wire-to-
Board Terminals,
28-32 AWG

This document was generated on 08/18/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION