

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0528070810

Status:

Active

Overview:

Easy-On FFC FPC Connectors

Description:

1.00mm Pitch Easy-On FFC/FPC Connector, Right-Angle, Non-ZIF, Top Contact Style Receptacle, 8 Circuits

Documents:

- 3D Model (PDF)

Product Specification PS-52807-003-001 (PDF)
- 3D Model

Packaging Specification SPK-52807-001-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Overview

Product Name

Taxonomy

UPC

FFC/FPC Connectors

52807

Easy-On FFC FPC Connectors

Easy-On

FFC / FPC Connectors

800754236126

Physical

Actuator Type

Circuits (Loaded)

Color - Resin

Contact Position

Flammability

Mated Height

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Mounting

PCB Retention

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Wire/Cable Type

Non-ZIF

8

Natural

Top

94V-0

3.60mm

Phosphor Bronze

Tin

Tin

High Temperature Thermoplastic

296.801/mg

1

Right Angle

3.20mm

Through Hole - Kinked Pin

None

Tray

1.00mm

1.00mm

0.914µm

0.914µm

Yes

No

No

-20° to +80°C

FFC/FPC

Electrical

Current - Maximum per Contact

Voltage - Maximum

0.2A, 0.4A, 0.5A

50V

Material Info

Reference - Drawing Numbers

Packaging Specification

SPK-52807-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

52807 Series

This document was generated on 01/18/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION