

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0430450412

Status:

Active

Overview:

Micro-Fit Connector System

Description:

Micro-Fit 3.0 Vertical Header, 3.00mm Pitch, Dual Row, 4 Circuits, with PCB Polarizing Peg, Tin, Glow-Wire Capable, Black

Documents:

- Drawing (PDF)

3D Model (PDF)

3D Model

Product Specification 430450001-PS-KO-000 (PDF)

Product Specification 430450001-PS-SP-000 (PDF)

Product Specification PS-43045-001 (PDF)

Packaging Specification PK-70873-0314-001 (PDF)
- Test Summary 430450004-TS-000 (PDF)

Test Summary TS-43045-001-001 (PDF)

Test Summary TS-46235-001-001 (PDF)

Datasheet (PDF)

Symbol Footprint Data SYM-43045-0412-001 (PDF)

Symbol Footprint Data SYM-43045-041X-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Comments

PCB Headers

43045

Power, Wire-to-Board

High Temperature|Square Pin|Offset Through Hole Mounting|Solder Type<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.

Micro-Fit Connector System

Micro-Fit 3.0

800753755482

Overview

Product Name

UPC

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Flammability

Glow-Wire Capable

Mated Height

Material - Metal

No

4

4

Black

30

94V-0

Yes

17.64mm

Brass



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

43045 Series

Mates With

Micro-Fit 3.0 Receptacle Housing [43025](#)  
. Micro-Fit 3.0 TPA Receptacle Housing  
[172952](#) . Micro-Fit 3.0 Cable Assembly  
[245132](#) , [214755](#) , [214756](#) . Micro-Fit TPA  
Cable Assembly [45132](#)

|                                                |                                                           |
|------------------------------------------------|-----------------------------------------------------------|
| Material - Plating Mating                      | Tin                                                       |
| Material - Plating Termination                 | Tin                                                       |
| Material - Resin                               | High Temperature Thermoplastic                            |
| Net Weight                                     | 0.733/g                                                   |
| Number of Rows                                 | 2                                                         |
| Orientation                                    | Vertical                                                  |
| PCB Locator                                    | Yes                                                       |
| PCB Retention                                  | Yes                                                       |
| PCB Thickness - Recommended                    | 1.60mm                                                    |
| Packaging Type                                 | Tray                                                      |
| Pitch - Mating Interface                       | 3.00mm                                                    |
| Plating min - Mating                           | 0.254μm                                                   |
| Polarized to PCB                               | Yes                                                       |
| Shrouded                                       | Fully                                                     |
| Stackable                                      | No                                                        |
| Surface Mount Compatible (SMC)                 | Yes                                                       |
| Temperature Range - Operating                  | -40° to +105°C                                            |
| Termination Interface: Style                   | Through Hole - Kinked Pin                                 |
| <b>Electrical</b>                              |                                                           |
| Current - Maximum per Contact                  | 8.5A                                                      |
| Voltage - Maximum                              | 600V                                                      |
| <b>Solder Process Data</b>                     |                                                           |
| Duration at Max. Process Temperature (seconds) | 030                                                       |
| Lead-freeProcess Capability                    | SMC&WAVE                                                  |
| Max. Cycles at Max. Process Temperature        | 003                                                       |
| Process Temperature max. C                     | 260                                                       |
| <b>Material Info</b>                           |                                                           |
| <b>Reference - Drawing Numbers</b>             |                                                           |
| Packaging Specification                        | PK-70873-0314-001                                         |
| Product Specification                          | 430450001-PS-KO-000, 430450001-PS-SP-000,<br>PS-43045-001 |
| Sales Drawing                                  | SD-43045-005-001                                          |
| Symbol/Footprint Data                          | SYM-43045-0412-001, SYM-43045-041X-001                    |
| Test Summary                                   | 430450004-TS-000, TS-43045-001-001,<br>TS-46235-001-001   |

This document was generated on 08/16/2021

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION