

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5600200220

Status:

Active

Overview:

DuraClik Connector System

Description:

DuraClik Wire-to-Board Header, Single Row, Vertical, 2 Circuits, Tin (Sn) Over Nickel, Natural

Documents:

3D Model (PDF)

3D Model

Drawing (PDF)


Product Specification PS-502351-001-001 (PDF)

Packaging Specification PK-560020-002-JP-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

|                                |                                                                                                                                                                                |
|--------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Agency Certification           |                                                                                                                                                                                |
| UL                             | E29179                                                                                                                                                                         |
| General                        |                                                                                                                                                                                |
| Product Family                 | PCB Headers                                                                                                                                                                    |
| Series                         | 560020                                                                                                                                                                         |
| Application                    | Automotive, Signal, Wire-to-Board                                                                                                                                              |
| Comments                       | The Operating Temperature Range when used with DuraClik series 502351 is -40°C to +105°C. It is -40°C to 125°C when used with DuraClik ISL series 560123 or TPA series 505151. |
| Overview                       | DuraClik Connector System                                                                                                                                                      |
| Product Name                   | DuraClik                                                                                                                                                                       |
| UPC                            | 887191747071                                                                                                                                                                   |
| Physical                       |                                                                                                                                                                                |
| Breakaway                      | No                                                                                                                                                                             |
| Circuits (Loaded)              | 2                                                                                                                                                                              |
| Circuits (maximum)             | 2                                                                                                                                                                              |
| Color - Resin                  | Natural                                                                                                                                                                        |
| Durability (mating cycles max) | 30                                                                                                                                                                             |
| First Mate / Last Break        | No                                                                                                                                                                             |
| Flammability                   | SC-0                                                                                                                                                                           |
| Glow-Wire Capable              | No                                                                                                                                                                             |
| Keying to Mating Part          | None                                                                                                                                                                           |
| Lock to Mating Part            | Yes                                                                                                                                                                            |
| Material - Metal               | Copper Alloy                                                                                                                                                                   |
| Material - Plating Mating      | Tin                                                                                                                                                                            |
| Material - Resin               | Polyamide                                                                                                                                                                      |
| Net Weight                     | 0.506/g                                                                                                                                                                        |
| Number of Rows                 | 1                                                                                                                                                                              |
| Orientation                    | Vertical                                                                                                                                                                       |
| PCB Locator                    | No                                                                                                                                                                             |
| PCB Retention                  | Yes                                                                                                                                                                            |
| Packaging Type                 | Embossed Tape on Reel                                                                                                                                                          |
| Pitch - Mating Interface       | 2.00mm                                                                                                                                                                         |
| Polarized to Mating Part       | Yes                                                                                                                                                                            |
| Polarized to PCB               | Yes                                                                                                                                                                            |
| Stackable                      | No                                                                                                                                                                             |
| Temperature Range - Operating  | -40° to +105°C, -40° to +125°C                                                                                                                                                 |
| Termination Interface: Style   | Surface Mount                                                                                                                                                                  |
| Electrical                     |                                                                                                                                                                                |
| Current - Maximum per Contact  | 3.0A                                                                                                                                                                           |



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

560020 Series

Mates With

DuraClik Crimp Housings [502351](#) , [560123](#) , [505151](#)

|                                                |                                      |
|------------------------------------------------|--------------------------------------|
| Voltage - Maximum                              | 125V AC (RMS)/DC                     |
| <b>Solder Process Data</b>                     |                                      |
| Duration at Max. Process Temperature (seconds) | 004                                  |
| Lead-freeProcess Capability                    | REFLOW                               |
| Max. Cycles at Max. Process Temperature        | 001                                  |
| Process Temperature max. C                     | 255                                  |
| <b>Material Info</b>                           |                                      |
| <b>Reference - Drawing Numbers</b>             |                                      |
| Packaging Specification                        | PK-560020-002-JP-001                 |
| Product Specification                          | PS-502351-001-001                    |
| Sales Drawing                                  | SD-560020-001-001, SD-560020-003-001 |

This document was generated on 08/18/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**