

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0877131001

Status:

Active

Overview:

Serial ATA Connectors

Description:

1.27mm Pitch Serial ATA Host Receptacle, Surface Mount, Vertical, Standard Height, with 3.70mm Plastic Locating Peg, 0.76µm Gold (Au) Selective Plating, 22 Circuits, Lead-Free

Documents:


3D Model

Packaging Specification PK-87713-100-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Specification PS-87713-016-001 (PDF)



Series image - Reference only

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		PCB Receptacles
Series		87713
Application		Board-to-Board, Signal
Comments		3.70mm Plastic Locating Peg
Overview		Serial ATA Connectors
Product Name		Serial ATA
UPC		822348699360
Physical		
(p)ower-(s)ignal Configuration		15p - 7s
Circuits (Loaded)		22
Circuits (maximum)		22
Durability (mating cycles max)		500
Flammability		94V-0
Glow-Wire Capable		No
Lock to Mating Part		Yes
Material - Metal		Copper Alloy
Material - Plating Mating		Gold
Material - Plating Termination		Tin
Material - Resin		High Temperature Thermoplastic
Net Weight		1.467/g
Number of Rows		1
Orientation		Vertical
PCB Locator		Yes
PCB Retention		None
Packaging Type		Tray
Pitch - Mating Interface		1.27mm
Plating min - Mating		0.762µm
Plating min - Termination		2.540µm
Polarized to Mating Part		Yes
Polarized to PCB		Yes
Surface Mount Compatible (SMC)		N/A
Temperature Range - Operating		-40° to +105°C
Termination Interface: Style		Surface Mount
Electrical		
Current - Maximum per Contact		1.5A
Voltage - Maximum		30V
Solder Process Data		
Duration at Max. Process Temperature (seconds)		010

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

87713 Series

Mates With

87679 , 87799 , 87703

Lead-free	Process Capability	REFLOW
Max. Cycles at Max. Process Temperature		001
Process Temperature max. C		260

Material Info

Reference - Drawing Numbers

Electrical Model Document	EE-78178-001-001, EE-78328-001-001, EE-78328-002-001, EE-87703-003-001, EE-87713-001-001
Packaging Specification	PK-87713-100-001
Product Specification	PS-87713-016-001
S-Parameter Model	SP-87713-001-001
Sales Drawing	SD-87713-001-001

This document was generated on 08/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION