

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5007620482

Status:

Active

Overview:

CMC and CMX Sealed, Hybrid, Modular Connectors

Description:

2.50mm, 3.50mm, 3.70mm CMC Header, Right-Angle, 48 Circuits, Gray

Documents:	
3D Model	Product Specification PS-64319-001-001 (PDF)
3D Model (PDF)	Datasheet (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	500762
Application	Automotive, Power, Wire-to-Board
Comments	Coding: Gray
Overview	CMC and CMX Sealed, Hybrid, Modular Connectors
Product Name	CMC
UPC	889056656313

Physical	
Breakaway	No
Circuits (Loaded)	48
Circuits (maximum)	48
Circuits Detail	8 x 1.5mm & 40 x 0.635mm terminals
Color - Resin	Gray
Durability (mating cycles max)	20
First Mate / Last Break	Yes
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	35.300/g
Number of Rows	4
Orientation	Right Angle
PC Tail Length	3.60mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.50mm, 3.50mm, 3.70mm
Pitch - Termination Interface	2.50mm, 3.50mm, 3.70mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Closed Ends
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Solder or Weld

Electrical	
Current - Maximum per Contact	12.0A, 2.5A
Voltage - Maximum	14V DC

Material Info



Series image - Reference only

EU ELV	
Compliant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
500762 Series

Mates With
CMC Receptacles [643201318](#) , [643203318](#)

Reference - Drawing Numbers

Product Specification
Sales Drawing

PS-64319-001-001
SD-500762-001-001

This document was generated on 02/02/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION