

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5015712007

Status:


Active

Overview:

Pico-Clasp Wire-to-Board Connectors

Description:

1.00mm Pitch, Pico-Clasp PCB Header, Dual Row, Right-Angle, Surface Mount, 0.10µm Gold Plated, Inner Positive Lock, 20 Circuits, Natural



Series image - Reference only

Documents:	
3D Model (PDF)	Product Specification 5011891000-PS-001 (PDF)
Drawing (PDF)	Application Specification 5011890000-AS-000 (PDF)
3D Model	Packaging Specification 5015719200-SPK-200 (PDF)
Product Specification 5011890000-PS-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	501571
Application	Signal, Wire-to-Board
Overview	Pico-Clasp Wire-to-Board Connectors
Product Name	Pico-Clasp
UPC	822348828401
Physical	
Breakaway	No
Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Nylon
Net Weight	626.500/mg
Number of Rows	2
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.102µm
Plating min - Termination	0.102µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	100V AC (RMS)/DC

Material Info

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
501571 Series

Mates With
Pico-Clasp Female Housing 501189

Reference - Drawing Numbers

Application Specification	5011890000-AS-000
Packaging Specification	5015719200-SPK-200
Product Specification	5011890000-PS-001, 5011891000-PS-001
Sales Drawing	5015710000-SD-000

This document was generated on 08/18/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION