

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [0901361105](#)  
**Status:** **Active**  
**Overview:** [C-Grid III Interconnects](#)  
**Description:** C-Grid III Header, Single Row, Vertical, Shrouded, 5 Circuits, 4µm Tin/Lead (Sn) over Nickel (Ni)

**Documents:**

|                                                               |                                                                  |
|---------------------------------------------------------------|------------------------------------------------------------------|
| <a href="#">3D Model</a>                                      | <a href="#">Application Specification 901190001-AS-000 (PDF)</a> |
| <a href="#">3D Model (PDF)</a>                                | <a href="#">Packaging Specification PK-90136-001-001 (PDF)</a>   |
| <a href="#">Drawing (PDF)</a>                                 | <a href="#">RoHS Certificate of Compliance (PDF)</a>             |
| <a href="#">Product Specification PS-99020-0001-001 (PDF)</a> |                                                                  |

**Agency Certification**


|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |                                          |
|----------------|------------------------------------------|
| Product Family | PCB Headers                              |
| Series         | <a href="#">90136</a>                    |
| Application    | Signal, Wire-to-Board                    |
| Overview       | <a href="#">C-Grid III Interconnects</a> |
| Product Name   | C-Grid III                               |
| UPC            | 800753532670                             |

**Physical**

|                                |                |
|--------------------------------|----------------|
| Breakaway                      | No             |
| Circuits (Loaded)              | 5              |
| Circuits (maximum)             | 5              |
| Color - Resin                  | Black          |
| First Mate / Last Break        | No             |
| Flammability                   | 94V-0          |
| Glow-Wire Capable              | No             |
| Guide to Mating Part           | No             |
| Keying to Mating Part          | None           |
| Lock to Mating Part            | Yes            |
| Material - Metal               | Brass          |
| Material - Plating Mating      | Tin            |
| Material - Plating Termination | Tin            |
| Material - Resin               | Polyester      |
| Net Weight                     | 0.890/g        |
| Number of Rows                 | 1              |
| Orientation                    | Vertical       |
| PC Tail Length                 | 2.90mm         |
| PCB Locator                    | No             |
| PCB Retention                  | None           |
| PCB Thickness - Recommended    | 1.60mm         |
| Packaging Type                 | Tray           |
| Pitch - Mating Interface       | 2.54mm         |
| Pitch - Termination Interface  | 2.54mm         |
| Plating min - Mating           | 3.048µm        |
| Plating min - Termination      | 3.048µm        |
| Polarized to PCB               | No             |
| Shrouded                       | Fully          |
| Stackable                      | No             |
| Temperature Range - Operating  | -55° to +125°C |
| Termination Interface: Style   | Through Hole   |



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**

[90136](#) Series

**Mates With**

[90123](#) C-Grid III Modular Crimp Housing,  
[90156](#) C-Grid III Crimp Housing

**Electrical**

|                               |            |
|-------------------------------|------------|
| Current - Maximum per Contact | 3.0A       |
| Voltage - Maximum             | 350V AC/DC |

**Solder Process Data**

|                                                |      |
|------------------------------------------------|------|
| Duration at Max. Process Temperature (seconds) | 005  |
| Lead-freeProcess Capability                    | WAVE |
| Max. Cycles at Max. Process Temperature        | 001  |
| Process Temperature max. C                     | 235  |

**Material Info**

**Reference - Drawing Numbers**

|                           |                   |
|---------------------------|-------------------|
| Application Specification | 901190001-AS-000  |
| Packaging Specification   | PK-90136-001-001  |
| Product Specification     | PS-99020-0001-001 |
| Sales Drawing             | SDA-90136-001     |

This document was generated on 08/24/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**