



INSTRUCTION MANUAL

Inductive Proximity Sensor	Rectangular-shaped
Front sensing	Top sensing
GX-F6 □	GX-H6 □

CMJE-GXFH6 No.0011-66V

Thank you very much for using SUNX products. Please read this Instruction Manual carefully and thoroughly for the correct and optimum use of this product. Kindly keep this manual in a convenient place for quick reference.

⚠ WARNING

- Never use this product as a sensing device for personnel protection.
- In case of using sensing devices for personnel protection, use products which meet laws and standards, such as OSHA, ANSI or IEC etc., for personnel protection applicable in each region or country.

1 CAUTIONS

- This product has been developed / produced for industrial use only.
- Make sure to check the wiring as wrong wiring will damage or burn the product.
- The output does not incorporate a short-circuit protection circuit. Do not connect it directly to a power supply or a capacitive load.
- Do not use during the initial transient time (50ms) after the power supply is switched on.
- Extension up to total 100m is possible with a 0.3mm², or more, cable.

2 MOUNTING

- Use the following sensor mounting bracket (optional) when mounting this product.
- M3 screws, nuts and washers are not attached to the sensor mounting brackets. Please arrange separately.

• MS-GL6-1



• MS-GL6-2




• MS-GX6-1




3 I/O CIRCUIT DIAGRAMS

• NPN output type



• PNP output type



4 INTENDED PRODUCTS FOR CE MARKING

- The model numbers specified in the "Catalog" comply with the CE Marking. As for the model numbers other than the "Catalog," contact our office.



SUNX Limited

URL : sunx.com

Overseas Sales Dept. (Head Office)

2431-1 Ushiyama-cho, Kasugai-shi, Aichi, 486-0901, Japan
Phone: +81-568-33-7861 FAX: +81-568-33-8591

Europe Headquarter: Panasonic Electric Works Europe AG

Rudolf-Diesel-Ring 2, D-83607 Holzkirchen, Germany
Phone: +49-8024-648-0

US Headquarter: Panasonic Electric Works Corporation of America

629 Central Avenue New Providence, New Jersey 07974 USA
Phone: +1-908-464-3550

PRINTED IN JAPAN