

# VAL-SPP-T2-275-1+1-UT-R - Type 2 surge arrester



1466212

<https://www.phoenixcontact.com/de/produkte/1466212>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in surge arrester, in accordance with Type 2/Class II, for 1-phase power supply networks with separate N and PE (3-conductor system: L1, N, PE), with remote indication contact.

## Your advantages

- Easy and safe installation with forward-thinking handling and safety features
- Reliable system protection with maximum performance and endurance
- Can be used in a wide range of applications due to the optimized design and broad portfolio
- Simple planning due to comprehensive digital data and selectors

## Commercial data

|                                      |                          |
|--------------------------------------|--------------------------|
| Item number                          | 1466212                  |
| Packing unit                         | 1 pc                     |
| Minimum order quantity               | 1 pc                     |
| Sales key                            | K1 - Überspannungsschutz |
| Product key                          | CL1381                   |
| GTIN                                 | 4063151857684            |
| Weight per piece (including packing) | 261,4 g                  |
| Weight per piece (excluding packing) | 236,7 g                  |
| Customs tariff number                | 85363030                 |
| Country of origin                    | DE                       |

# VAL-SPP-T2-275-1+1-UT-R - Type 2 surge arrester



1466212

<https://www.phoenixcontact.com/de/produkte/1466212>

## Technical data

### Notes

#### General

|      |                                                                                                                                                                                                                                                                              |
|------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note | For pollution degree 3 and wiring with fork cable lugs, an additional minimum lateral distance of 1 mm to earthed conductive surfaces must be maintained for cross-sections $\geq 16 \text{ mm}^2$ .<br>No additional lateral distances are required for pollution degree 2. |
|------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### Product properties

|                                |                                   |
|--------------------------------|-----------------------------------|
| Product type                   | Surge arrester                    |
| IEC test classification        | II                                |
|                                | T2                                |
| EN type                        | T2                                |
| IEC power supply system        | TN-S                              |
|                                | TT                                |
| Type                           | Base element, DIN rail mounting   |
| Number of positions            | 2                                 |
| Surge protection fault message | Optical, remote indicator contact |

#### Data management status

|                  |    |
|------------------|----|
| Article revision | 02 |
|------------------|----|

#### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree     | 3   |

### Electrical properties

|                         |               |
|-------------------------|---------------|
| Nominal frequency $f_N$ | 50 Hz (60 Hz) |
|-------------------------|---------------|

#### Indicator/remote signaling

|                            |                                                                                                                                   |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Connection name            | Remote fault indicator contact                                                                                                    |
| Switching function         | Changeover contact                                                                                                                |
| Max. required back-up fuse | 1 A (gG)                                                                                                                          |
| AC operating voltage       | 5 V AC ... 250 V AC ( $\leq 2000 \text{ m (amsl)}$ at pollution degree 2)<br>5 V AC ... 150 V AC ( $\leq 5000 \text{ m (amsl)}$ ) |
| AC operating current       | 5 mA AC ... 1 A AC                                                                                                                |
| DC operating voltage       | 30 V DC ( $\leq 5000 \text{ m (amsl)}$ )                                                                                          |
| DC operating current       | 1 A DC                                                                                                                            |
| DC operating voltage       | 125 V DC ( $\leq 5000 \text{ m (amsl)}$ )                                                                                         |
| DC operating current       | 200 mA DC                                                                                                                         |
| Insulation type            | The product has double/reinforced insulation between the main and auxiliary circuit.                                              |

# VAL-SPP-T2-275-1+1-UT-R - Type 2 surge arrester



1466212

<https://www.phoenixcontact.com/de/produkte/1466212>


## Connection data

|                                                                       |                                                                                                                                                          |
|-----------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Connection method                                                     | Screw connection                                                                                                                                         |
| Screw thread                                                          | M5                                                                                                                                                       |
| Tightening torque                                                     | 3 Nm ... 3.5 Nm                                                                                                                                          |
| Stripping length                                                      | 18 mm                                                                                                                                                    |
| Conductor cross section flexible                                      | 1.5 mm <sup>2</sup> ... 35 mm <sup>2</sup> (without ferrule)<br>2x 1.5 mm <sup>2</sup> ... 16 mm <sup>2</sup> (2 conductors with the same cross-section) |
| Conductor cross section rigid                                         | 1.5 mm <sup>2</sup> ... 50 mm <sup>2</sup><br>2x 1.5 mm <sup>2</sup> ... 16 mm <sup>2</sup> (2 conductors with the same cross-section)                   |
| Conductor cross section AWG                                           | 15 ... 2                                                                                                                                                 |
| Conductor cross section, flexible, with ferrule, with plastic sleeve  | 1.5 mm <sup>2</sup> ... 35 mm <sup>2</sup><br>2x 1.5 mm <sup>2</sup> ... 10 mm <sup>2</sup> (2 conductors with the same cross-section)                   |
| Conductor cross section flexible, with ferrule without plastic sleeve | 1.5 mm <sup>2</sup> ... 25 mm <sup>2</sup><br>2x 1.5 mm <sup>2</sup> ... 16 mm <sup>2</sup> (2 conductors with the same cross-section)                   |
| Connection method                                                     | Fork-type cable lug                                                                                                                                      |
| Conductor cross section flexible                                      | 1.5 mm <sup>2</sup> ... 25 mm <sup>2</sup>                                                                                                               |

## Remote fault indicator contact

|                                                                       |                                               |
|-----------------------------------------------------------------------|-----------------------------------------------|
| Connection method                                                     | Push-in connection                            |
| Stripping length                                                      | 8 mm                                          |
| Conductor cross section flexible                                      | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>  |
| Conductor cross section rigid                                         | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>  |
| Conductor cross section AWG                                           | 24 ... 16                                     |
| Conductor cross section, flexible, with ferrule, with plastic sleeve  | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>  |
| Conductor cross section flexible, with ferrule without plastic sleeve | 0.25 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> |

## Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 35.6 mm                                                                              |
| Height              | 109.1 mm                                                                             |
| Depth               | 71.5 mm (incl. DIN rail 7.5 mm)                                                      |
| Horizontal pitch    | 2 Div.                                                                               |

## Material specifications

|       |                                          |
|-------|------------------------------------------|
| Color | gray (RAL 7042)<br>light gray (RAL 7035) |
|-------|------------------------------------------|

# VAL-SPP-T2-275-1+1-UT-R - Type 2 surge arrester



1466212

<https://www.phoenixcontact.com/de/produkte/1466212>

|                                        |                   |
|----------------------------------------|-------------------|
| Flammability rating according to UL 94 | V-0               |
| CTI value of material                  | 600               |
| Insulating material                    | PA 6.6-FR 20 % GF |
|                                        | PBT               |
| Material group                         | I                 |
| Housing material                       | PA 6.6-FR 20 % GF |
|                                        | PBT               |

## Protective circuit

|                                                    |                                        |
|----------------------------------------------------|----------------------------------------|
| Mode of protection                                 | L-N                                    |
|                                                    | L-PE                                   |
|                                                    | N-PE                                   |
| Nominal voltage $U_N$                              | 240/415 V AC $\pm 10\%$ (TN-S)         |
|                                                    | 240/415 V AC $\pm 10\%$ (TT)           |
| Nominal frequency $f_N$                            | 50 Hz (60 Hz)                          |
| Maximum continuous operating voltage $U_C$ (L-N)   | 275 V AC                               |
| Maximum continuous operating voltage $U_C$ (L-PE)  | 275 V AC                               |
| Maximum continuous operating voltage $U_C$ (N-PE)  | 305 V AC                               |
| Rated load current $I_L$                           | 80 A (25 mm <sup>2</sup> )             |
| Residual current $I_{PE}$                          | $\leq 5 \mu A$                         |
| Standby power consumption $P_C$                    | $\leq 120.00$ mVA                      |
| Nominal discharge current $I_n$ (8/20) $\mu s$     | 20 kA                                  |
| Maximum discharge current $I_{max}$ (8/20) $\mu s$ | 40 kA                                  |
| Total discharge current $I_{total}$ (8/20) $\mu s$ | 40 kA                                  |
| Follow current interrupt rating $I_{fi}$ (N-PE)    | 100 A                                  |
| Short-circuit current rating $I_{SCCR}$            | 50 kA                                  |
| Voltage protection level $U_p$ (L-N)               | $\leq 1.35$ kV                         |
| Voltage protection level $U_p$ (L-PE)              | $\leq 1.6$ kV                          |
| Voltage protection level $U_p$ (N-PE)              | $\leq 1.5$ kV                          |
| Residual voltage $U_{res}$ (L-N)                   | $\leq 1.35$ kV (at $I_n$ )             |
|                                                    | $\leq 1.1$ kV (at 10 kA)               |
|                                                    | $\leq 1$ kV (at 5 kA)                  |
|                                                    | $\leq 0.9$ kV (at 3 kA)                |
| Residual voltage $U_{res}$ (L-PE)                  | $\leq 1.6$ kV (at $I_n$ )              |
|                                                    | $\leq 1.3$ kV (at 10 kA)               |
|                                                    | $\leq 1.1$ kV (at 5 kA)                |
|                                                    | $\leq 1$ kV (at 3 kA)                  |
| Residual voltage $U_{res}$ (N-PE)                  | $\leq 0.5$ kV (at $I_n$ )              |
|                                                    | $\leq 0.4$ kV (at 10 kA)               |
|                                                    | $\leq 0.3$ kV (at 5 kA)                |
|                                                    | $\leq 0.1$ kV (at 3 kA)                |
| TOV behavior at $U_T$ (L-N)                        | 350 V AC (5 s / withstand mode)        |
|                                                    | 460 V AC (120 min / safe failure mode) |
| TOV behavior at $U_T$ (L-PE)                       | 1464 V AC (200 ms/withstand mode)      |

# VAL-SPP-T2-275-1+1-UT-R - Type 2 surge arrester



1466212

<https://www.phoenixcontact.com/de/produkte/1466212>

|                                             |                                     |
|---------------------------------------------|-------------------------------------|
| TOV behavior at $U_T$ (N-PE)                | 1200 V AC (200 ms / withstand mode) |
| Response time $t_A$ (L-N)                   | $\leq 25$ ns                        |
| Response time $t_A$ (L-PE)                  | $\leq 100$ ns                       |
| Response time $t_A$ (N-PE)                  | $\leq 100$ ns                       |
| Max. backup fuse with V-type through wiring | 80 A (gG)                           |
| Max. backup fuse with branch wiring         | 315 A (gG)                          |

## Environmental and real-life conditions

### Ambient conditions

|                                         |                                                     |
|-----------------------------------------|-----------------------------------------------------|
| Degree of protection                    | IP20C (Installed)                                   |
| Ambient temperature (operation)         | -40 °C ... 85 °C                                    |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C                                    |
| Ambient temperature (assembly)          | -5 °C ... 50 °C                                     |
| Altitude                                | $\leq 5000$ m (amsl)                                |
| Permissible humidity (operation)        | 5 % ... 95 %                                        |
| Shock (operation)                       | 25g (Half-sine / 11 ms / $3x \pm X, \pm Y, \pm Z$ ) |
| Vibration (operation)                   | 5g (10 ... 500 Hz / 2.5 h / X, Y, Z)                |

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standards/specifications | IEC 61643-11    |
| Note                     | 2011            |
| Standards/specifications | EN 61643-11     |
| Note                     | 2012 + A11:2018 |

## Mounting

|               |                 |
|---------------|-----------------|
| Mounting type | DIN rail: 35 mm |
|---------------|-----------------|


# VAL-SPP-T2-275-1+1-UT-R - Type 2 surge arrester

1466212


<https://www.phoenixcontact.com/de/produkte/1466212>

## Drawings

Circuit diagram



Dimensional drawing



# VAL-SPP-T2-275-1+1-UT-R - Type 2 surge arrester



1466212

<https://www.phoenixcontact.com/de/produkte/1466212>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/de/produkte/1466212>



**IECEE CB Scheme**

Approval ID: NL-109184

**CCA**

Approval ID: NTR NL-8052



**KEMA-KEUR**

Approval ID: 71-138153 REV.2

# VAL-SPP-T2-275-1+1-UT-R - Type 2 surge arrester



1466212

<https://www.phoenixcontact.com/de/produkte/1466212>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27130805 |
| ECLASS-13.0 | 27171202 |

# VAL-SPP-T2-275-1+1-UT-R - Type 2 surge arrester



1466212

<https://www.phoenixcontact.com/de/produkte/1466212>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

# VAL-SPP-T2-275-1+1-UT-R - Type 2 surge arrester



1466212

<https://www.phoenixcontact.com/de/produkte/1466212>

## Accessories

### EMG-GKS 12 - Marking material

2947035

<https://www.phoenixcontact.com/de/produkte/2947035>



Device marking label, width: 12 mm, area: 12 x 8 mm, e.g. for EML(10x7) R adhesive marking material

---

### EML (10X7)R - Label

0816663

<https://www.phoenixcontact.com/de/produkte/0816663>



Label, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, lettering field size: 10 x 7 mm, Number of individual labels: 10000

# VAL-SPP-T2-275-1+1-UT-R - Type 2 surge arrester



1466212

<https://www.phoenixcontact.com/de/produkte/1466212>

## VAL-SPP-T2-275-P - Type 2 surge protection plug

1466685

<https://www.phoenixcontact.com/de/produkte/1466685>



Type 2 surge protection plug for VAL-SPP base element, thermally monitored, optical red/green status indicator.

---

## VAL-SPP-T2-NPE-P - Type 2 surge protection plug

1466689

<https://www.phoenixcontact.com/de/produkte/1466689>



Type 2 surge protection plug, with N-PE total current spark gap for VAL-SPP base element, thermal monitoring, optical red/green status indicator.

# VAL-SPP-T2-275-1+1-UT-R - Type 2 surge arrester




1466212

<https://www.phoenixcontact.com/de/produkte/1466212>

## VAL-SPP-T2-BE-1+1-UT - Type 2 surge protection base element

1466703

<https://www.phoenixcontact.com/de/produkte/1466703>



Base element for type 2 arresters from the VAL-SPP product family. Version for 1-phase power supplies with separate cable routing of N and PE.

---

## SPP-R-2 - Remote signaling module

1466699

<https://www.phoenixcontact.com/de/produkte/1466699>



Optional remote signaling module for 2-pos. SPDs and base elements from the VALVETRAB SPP product family.

---

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Deutschland GmbH  
Flachsmarktstraße 8  
D-32825 Blomberg  
+49 52 35/3-1 20 00  
[info@phoenixcontact.de](mailto:info@phoenixcontact.de)