

VAL-SPP-T2-275-3+1-UT - Type 2 surge arrester



1466213

<https://www.phoenixcontact.com/de/produkte/1466213>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in surge arrester, in accordance with Type 2/Class II, for 3-phase power supply networks with separate N and PE (5-conductor system: L1, L2, L3, N, PE).

Your advantages

- Easy and safe installation with forward-thinking handling and safety features
- Reliable system protection with maximum performance and endurance
- Can be used in a wide range of applications due to the optimized design and broad portfolio
- Simple planning due to comprehensive digital data and selectors

Commercial data

Item number	1466213
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	K1 - Überspannungsschutz
Product key	CL1381
GTIN	4063151860110
Weight per piece (including packing)	457 g
Weight per piece (excluding packing)	426 g
Customs tariff number	85363030
Country of origin	DE

VAL-SPP-T2-275-3+1-UT - Type 2 surge arrester



1466213

<https://www.phoenixcontact.com/de/produkte/1466213>

Technical data

Notes

General

Note	For pollution degree 3 and wiring with fork cable lugs, an additional minimum lateral distance of 1 mm to earthed conductive surfaces must be maintained for cross-sections $\geq 16 \text{ mm}^2$. No additional lateral distances are required for pollution degree 2.
------	--

Product properties

Product type	Surge arrester
IEC test classification	II
	T2
EN type	T2
IEC power supply system	TN-S
	TT
Number of positions	4
Surge protection fault message	optical

Data management status

Article revision	01
------------------	----

Insulation characteristics

Overvoltage category	III
Pollution degree	3

Electrical properties

Nominal frequency f_N	50 Hz (60 Hz)
-------------------------	---------------

Connection data

Connection method	Screw connection
Screw thread	M5
Tightening torque	3 Nm ... 3.5 Nm
Stripping length	18 mm
Conductor cross section flexible	1.5 mm ² ... 35 mm ² (without ferrule)
	2x 1.5 mm ² ... 16 mm ² (2 conductors with the same cross-section)
Conductor cross section rigid	1.5 mm ² ... 50 mm ²
	2x 1.5 mm ² ... 16 mm ² (2 conductors with the same cross-section)
Conductor cross section AWG	15 ... 2
Conductor cross section, flexible, with ferrule, with plastic sleeve	1.5 mm ² ... 35 mm ²
	2x 1.5 mm ² ... 10 mm ² (2 conductors with the same cross-section)

VAL-SPP-T2-275-3+1-UT - Type 2 surge arrester




1466213

<https://www.phoenixcontact.com/de/produkte/1466213>

Conductor cross section flexible, with ferrule without plastic sleeve	1.5 mm ² ... 25 mm ²
	2x 1.5 mm ² ... 16 mm ² (2 conductors with the same cross-section)
Connection method	Fork-type cable lug
Conductor cross section flexible	1.5 mm ² ... 25 mm ²

Dimensions

Dimensional drawing	
Width	71.2 mm
Height	96.6 mm
Depth	71.5 mm (incl. DIN rail 7.5 mm)
Horizontal pitch	4 Div.

Material specifications

Color	gray (RAL 7042)
	light gray (RAL 7035)
Flammability rating according to UL 94	V-0
CTI value of material	600
Insulating material	PA 6.6-FR 20 % GF
	PBT
Material group	I
Housing material	PA 6.6-FR 20 % GF
	PBT

Protective circuit

Mode of protection	L-N
	L-PE
	N-PE
Nominal voltage U_N	240/415 V AC ± 10 % (TN-S)
	240/415 V AC ± 10 % (TT)
Nominal frequency f_N	50 Hz (60 Hz)
Maximum continuous operating voltage U_C (L-N)	275 V AC
Maximum continuous operating voltage U_C (L-PE)	275 V AC
Maximum continuous operating voltage U_C (N-PE)	305 V AC
Rated load current I_L	80 A (25 mm ²)
Residual current I_{PE}	$\leq 5 \mu A$
Standby power consumption P_C	≤ 360.00 mVA
Nominal discharge current I_n (8/20) μs	20 kA
Maximum discharge current I_{max} (8/20) μs	40 kA
Total discharge current I_{total} (8/20) μs	40 kA

VAL-SPP-T2-275-3+1-UT - Type 2 surge arrester



1466213

<https://www.phoenixcontact.com/de/produkte/1466213>

Follow current interrupt rating I_{fi} (N-PE)	100 A
Short-circuit current rating I_{SCCR}	50 kA
Voltage protection level U_p (L-N)	≤ 1.35 kV
Voltage protection level U_p (L-PE)	≤ 1.6 kV
Voltage protection level U_p (N-PE)	≤ 1.5 kV
Residual voltage U_{res} (L-N)	≤ 1.35 kV (at I_n)
	≤ 1.1 kV (at 10 kA)
	≤ 1 kV (at 5 kA)
	≤ 0.9 kV (at 3 kA)
Residual voltage U_{res} (L-PE)	≤ 1.6 kV (at I_n)
	≤ 1.3 kV (at 10 kA)
	≤ 1.1 kV (at 5 kA)
	≤ 1 kV (at 3 kA)
Residual voltage U_{res} (N-PE)	≤ 0.5 kV (at I_n)
	≤ 0.4 kV (at 10 kA)
	≤ 0.3 kV (at 5 kA)
	≤ 0.1 kV (at 3 kA)
TOV behavior at U_T (L-N)	350 V AC (5 s / withstand mode)
	460 V AC (120 min / safe failure mode)
TOV behavior at U_T (L-PE)	1464 V AC (200 ms/withstand mode)
TOV behavior at U_T (N-PE)	1200 V AC (200 ms / withstand mode)
Response time t_A (L-N)	≤ 25 ns
Response time t_A (L-PE)	≤ 100 ns
Response time t_A (N-PE)	≤ 100 ns
Max. backup fuse with V-type through wiring	80 A (gG)
Max. backup fuse with branch wiring	315 A (gG)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20C (Installed)
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Altitude	≤ 5000 m (amsl)
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	25g (Half-sine / 11 ms / 3x $\pm X$, $\pm Y$, $\pm Z$)
Vibration (operation)	5g (10 ... 500 Hz / 2.5 h / X, Y, Z)

Standards and regulations

Standards/specifications	IEC 61643-11
Note	2011
Standards/specifications	EN 61643-11
Note	2012 + A11:2018

VAL-SPP-T2-275-3+1-UT - Type 2 surge arrester



1466213

<https://www.phoenixcontact.com/de/produkte/1466213>

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------


VAL-SPP-T2-275-3+1-UT - Type 2 surge arrester

1466213


<https://www.phoenixcontact.com/de/produkte/1466213>

Drawings

Circuit diagram



Dimensional drawing



VAL-SPP-T2-275-3+1-UT - Type 2 surge arrester



1466213

<https://www.phoenixcontact.com/de/produkte/1466213>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/de/produkte/1466213>



IECEE CB Scheme

Approval ID: NL-109184

CCA

Approval ID: NTR NL-8052



KEMA-KEUR

Approval ID: 71-138153 REV.2

VAL-SPP-T2-275-3+1-UT - Type 2 surge arrester



1466213

<https://www.phoenixcontact.com/de/produkte/1466213>

Classifications

ECLASS

ECLASS-11.0	27130805
ECLASS-13.0	27171202

VAL-SPP-T2-275-3+1-UT - Type 2 surge arrester



1466213

<https://www.phoenixcontact.com/de/produkte/1466213>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

VAL-SPP-T2-275-3+1-UT - Type 2 surge arrester



1466213

<https://www.phoenixcontact.com/de/produkte/1466213>

Accessories

EMG-GKS 12 - Marking material

2947035

<https://www.phoenixcontact.com/de/produkte/2947035>



Device marking label, width: 12 mm, area: 12 x 8 mm, e.g. for EML(10x7) R adhesive marking material

EML (10X7)R - Label

0816663

<https://www.phoenixcontact.com/de/produkte/0816663>



Label, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, lettering field size: 10 x 7 mm, Number of individual labels: 10000

VAL-SPP-T2-275-3+1-UT - Type 2 surge arrester



1466213


<https://www.phoenixcontact.com/de/produkte/1466213>

SPP-R-4 - Remote signaling module

1466701

<https://www.phoenixcontact.com/de/produkte/1466701>

Optional remote signaling module for 4-pos. surge arresters and base elements from the VALVETRAB SPP product family.



VAL-SPP-T2-275-P - Type 2 surge protection plug

1466685

<https://www.phoenixcontact.com/de/produkte/1466685>

Type 2 surge protection plug for VAL-SPP base element, thermally monitored, optical red/green status indicator.



VAL-SPP-T2-275-3+1-UT - Type 2 surge arrester



1466213

<https://www.phoenixcontact.com/de/produkte/1466213>

VAL-SPP-T2-NPE-P - Type 2 surge protection plug

1466689

<https://www.phoenixcontact.com/de/produkte/1466689>




Type 2 surge protection plug, with N-PE total current spark gap for VAL-SPP base element, thermal monitoring, optical red/green status indicator.

VAL-SPP-T2-BE-3+1-UT - Type 2 surge protection base element

1466705

<https://www.phoenixcontact.com/de/produkte/1466705>



Base element for type 2/Class II arresters from the VALVETRAB SPP product family. Version for 3-phase power supply networks with separate N and PE (5-conductor system: L1, L2, L3, N, PE).

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstraße 8
D-32825 Blomberg
+49 52 35/3-1 20 00
info@phoenixcontact.de