

## Heat shrinking Tube Service Kit, White

Item No. : 2004CA099



This range is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics and the laboratory needs. Shrinking ration 2:1 standard for a range of application diameter from 2.0 to 16.5 mm.

The heat-shrink tubing can be used for insulation, protective covering of components, as anti-kink protection, protection against corrosion, as well as repair of cables and lines, and much more be used.

<b>Shrinking ratio</b>	<b>2 : 1</b>
<b>Material</b>	<b>PE</b>
<b>Shrinking temperature</b>	<b>70°C - 110°C</b>
<b>Operation temperature</b>	<b>-55°C - 110°C</b>
<b>Flammability</b>	<b>VW-1</b>
<b>Tensile strength</b>	<b>≥ 10.3 Mpa</b>
<b>Elongation at break</b>	<b>≥ 300%</b>
<b>Rated voltage</b>	<b>600V</b>
<b>Diselectric strength</b>	<b>≥ 1.5kv/mm at 30sec.</b>
<b>Volume resistivity</b>	<b>≥ 10<sup>14</sup>Ω</b>

### set contents

Heat shrink tube		Length
Inner diameter ø	after shrink ø	
2.0 mm	0.85 mm	3 m
3.0 mm	1.30 mm	3 m
4.0 mm	1.80 mm	3 m
6.5 mm	3.00 mm	2 m
8.5 mm	4.00 mm	2 m
12.5 mm	6.00 mm	1.5 m
16.5 mm	8.00 mm	1 m