


Heat shrink tube 2:1 assortment 620 pcs Type: 2103CA001

This range is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics and the laboratory needs.

620 pieces of shrinking ratio 2:1 standard shrinking tube for a range of application diameter from 1.0 to 13.0 mm.

The heat-shrink tubing can be used for insulation, protective covering of components, as anti-kink protection, protection against corrosion, as well as repair of cables and lines, and much more.



Technical Specifications

Material: PE • Shrink ratio: 2:1 • Shrinking temperature: 80°C ... 125°C • Operation temperature: -20°C ... 130°C • Flammability: VW-1 • Tensile strength: 10 Mpa • Rated voltage: 600 V

Content

Quantity x Internal Diameter x Single Length x Color:

120pcs x 1.0mm x 45mm Black / 95pcs x 1.5mm x 45mm Red / 75pcs x 2.0mm x 45mm Yellow / 55pcs x 2.5mm x 45mm Blue / 55pcs x 3.5mm x 45mm Green / 45pcs x 4.0mm x 45mm Red / 45pcs x 4.0mm x 45mm Black 35pcs x 5.0mm x 45mm Blue / 20pcs x 6.0mm x 45mm Blue / 30pcs x 7.0mm x 45mm Red 25pcs x 10.0mm x 45mm Black / 20pcs x 13.0mm x 45mm Black