


Heat-Shrink-Tube Reels 2:1 Item-No.: 24CA261 ... 24CA281



These high-quality shrink sleeves are particularly suitable for service workshops, electronics technicians and applications with a high demand for shrink tubing. The black heat-shrink tube is wound onto a cardboard reel and can therefore be cut to length individually. Various available nominal diameters open up a wide range of applications. The standard version with a shrink ratio of 2:1 without internal adhesive is ideal for most applications.

Technical Specifications

Material: PE • Shrink ratio: 2:1 • Shrink temperature (min.): 90 °C • Shrink temperature (max.): 125 °C • Operating temperature: -40 °C ... +125 °C • Tensile strength (min.): 10.4 MPa • Dielectric strength 15 kV/mm (30 sec.) • Rated voltage: 600 V • Elongation break: min. 300% • Color: Black.

Item-No.	Description	Diameter	Wall thickness material	Wall thickness shrunk	Content	EAN/GTIN
24CA261	Shrinking tube 2:1 black Φ 1 mm	1 mm	0.16 (± 0.02) mm	0.32 (± 0.04) mm	200 m	4260732287001
24CA262	Shrinking tube 2:1 black Φ 2 mm	2 mm	0.18 (± 0.02) mm	0.36 (± 0.04) mm	200 m	4260732287018
24CA263	Shrinking tube 2:1 black Φ 4 mm	4 mm	0.19 (± 0.02) mm	0.38 (± 0.04) mm	200 m	4260732287025
24CA264	Shrinking tube 2:1 black Φ 6 mm	6 mm	0.21 (± 0.02) mm	0.42 (± 0.04) mm	100 m	4260732287032
24CA265	Shrinking tube 2:1 black Φ 8 mm	8 mm	0.21 (± 0.02) mm	0.42 (± 0.04) mm	100 m	4260732287049
24CA266	Shrinking tube 2:1 black Φ 10 mm	10 mm	0.22 (± 0.02) mm	0.44 (± 0.04) mm	100 m	4260732287056
24CA267	Shrinking tube 2:1 black Φ 12 mm	12 mm	0.23 (± 0.02) mm	0.46 (± 0.04) mm	100 m	4260732287063
24CA268	Shrinking tube 2:1 black Φ 14 mm	14 mm	0.23 (± 0.02) mm	0.46 (± 0.04) mm	100 m	4260732287070
24CA269	Shrinking tube 2:1 black Φ 16 mm	16 mm	0.24 (± 0.02) mm	0.48 (± 0.04) mm	100 m	4260732287087
24CA270	Shrinking tube 2:1 black Φ 18 mm	18 mm	0.24 (± 0.02) mm	0.48 (± 0.04) mm	50 m	4260732287094
24CA271	Shrinking tube 2:1 black Φ 20 mm	20 mm	0.25 (± 0.02) mm	0.5 (± 0.04) mm	50 m	4260732287100
24CA272	Shrinking tube 2:1 black Φ 25 mm	25 mm	0.27 (± 0.03) mm	0.54 (± 0.06) mm	50 m	4260732287117
24CA273	Shrinking tube 2:1 black Φ 30 mm	30 mm	0.28 (± 0.03) mm	0.56 (± 0.06) mm	25 m	4260732287124
24CA274	Shrinking tube 2:1 black Φ 35 mm	35 mm	0.29 (± 0.03) mm	0.58 (± 0.06) mm	25 m	4260732287131
24CA275	Shrinking tube 2:1 black Φ 40 mm	40 mm	0.3 (± 0.03) mm	0.6 (± 0.06) mm	25 m	4260732287148
24CA276	Shrinking tube 2:1 black Φ 50 mm	50 mm	0.33 (± 0.03) mm	0.66 (± 0.06) mm	25 m	4260732287155
24CA277	Shrinking tube 2:1 black Φ 60 mm	60 mm	0.35 (± 0.03) mm	0.7 (± 0.06) mm	25 m	4260732287162
24CA278	Shrinking tube 2:1 black Φ 70 mm	70 mm	0.38 (± 0.03) mm	0.76 (± 0.06) mm	25 m	4260732287179
24CA279	Shrinking tube 2:1 black Φ 80 mm	80 mm	0.4 (± 0.03) mm	0.8 (± 0.06) mm	25 m	4260732287186
24CA280	Shrinking tube 2:1 black Φ 90 mm	90 mm	0.45 (± 0.03) mm	0.9 (± 0.06) mm	25 m	4260732287193
24CA281	Shrinking tube 2:1 black Φ 100 mm	100 mm	0.49 (± 0.03) mm	0.89 (± 0.06) mm	25 m	4260732287209