

## SAFETY DATA SHEET

## Graduate Acrylic White

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

## 1.1. Product identifier

## Trade name

Graduate Acrylic White

## Product no.

D123100011

## 1.2. Relevant identified uses of the substance or mixture and uses advised against

## Relevant identified uses of the substance or mixture

Art supplies and hobby preparations

## Use descriptors (UK REACH)

Sectors of use	Description
LCS "C"	Consumer uses: Private households (= general public = consumers)

Product category	Description
PC 9a	Coatings and Paints, Fillers, Putties, Thinners

Process category	Description
PROC 10	Roller application or brushing

## Uses advised against

None known.

## 1.3. Details of the supplier of the safety data sheet

## ▼ Company and address

**Daler-Rowney Ltd.**

Peacock Lane Bracknell

RG12 8ST Bracknell

United Kingdom

+44 1344 461 156 (0730 – 1600 GMT)

www.daler-rowney.com

## Contact person

Research and Development

## Revision

05/06/2024

## SDS Version

2.0

## Date of previous version

12/02/2024 (1.0)

## 1.4. Emergency telephone number

Contact The National Poisons Information Service (dial 111, 24 h service).

See section 4 "First aid measures".

## SECTION 2: Hazards identification

## 2.1. Classification of the substance or mixture

Not classified according to Regulation (EC) No. 1272/2008 (CLP) as retained and amended in UK law.

## 2.2. Label elements

## Hazard pictogram(s)

Not applicable.

## Signal word

Not applicable.

**Hazard statement(s)**

Not applicable.

**Precautionary statement(s)**

General

-

Prevention

-

Response

-

Storage

-

Disposal

-

**Hazardous substances**

1,2-benzisothiazol-3(2H)-one;1,2-benzisothiazolin-3-one

**▼ Additional labelling**

 EUH208, Contains reaction mass of 5-chloro-2-methyl-2H-isothiazol-3-one and 2-methyl-2H-isothiazol-3-one (3:1).  
 May produce an allergic reaction.

EUH210, Safety data sheet available on request.

**2.3. Other hazards**
**Additional warnings**

 This mixture/product does not contain any substances known to fulfil the criteria for PBT and vPvB classification.  
 This product does not contain any substances considered to be endocrine disruptors in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605.

**SECTION 3: Composition/information on ingredients**
**3.1. Substances**

Not applicable. This product is a mixture.

**3.2. ▼ Mixtures**

Product/substance	Identifiers	% w/w	Classification	Note
2-aminoethanol;ethanolamine	CAS No.: 141-43-5 EC No.: 205-483-3 UK-REACH: Index No.: 603-030-00-8	<0.25%	Acute Tox. 4, H302 Acute Tox. 4, H312 Skin Corr. 1B, H314 Eye Dam. 1, H318 Acute Tox. 4, H332 STOT SE 3, H335 Aquatic Chronic 3, H412	[1]
1,2-benzisothiazol-3(2H)-one;1,2-benzisothiazolin-3-one	CAS No.: 2634-33-5 EC No.: 220-120-9 UK-REACH: Index No.: 613-088-00-6	<0.05%	Acute Tox. 4, H302 Skin Irrit. 2, H315 Skin Sens. 1, H317 Eye Dam. 1, H318 Aquatic Acute 1, H400 (M=10)	
reaction mass of 5-chloro-2-methyl-2H-isothiazol-3-one and 2-methyl-2H-isothiazol-3-one (3:1)	CAS No.: 55965-84-9 EC No.: 611-341-5 UK-REACH: Index No.: 613-167-00-5	<0.0015%	EUH071 Acute Tox. 3, H301 Acute Tox. 2, H310 Skin Corr. 1C, H314 (SCL: 0.60 %) Skin Irrit. 2, H315 (SCL: 0.06 %) Skin Sens. 1A, H317 (SCL: 0.0015 %) Eye Dam. 1, H318 (SCL: 0.60 %) Eye Irrit. 2, H319 (SCL: 0.06 %) Acute Tox. 2, H330 Aquatic Acute 1, H400 (M=100) Aquatic Chronic 1, H410 (M=100)	

See full text of H-phrases in section 16. Occupational exposure limits are listed in section 8, if these are available.

#### Other information

[1] European occupational exposure limit.

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

##### General information

In the case of accident: Contact a doctor or casualty department – take the label or this safety data sheet. Contact a doctor if in doubt about the injured person's condition or if the symptoms persist. Never give an unconscious person water or other drink.

##### Inhalation

Upon breathing difficulties or irritation of the respiratory tract: Bring the person into fresh air and stay with him/her.

##### ▼ Skin contact

IF ON SKIN: Wash with plenty of water and soap.

Remove contaminated clothing and shoes. Ensure to wash exposed skin thoroughly with water and soap. DO NOT use solvents or thinners.

If skin irritation occurs: Get medical advice/attention.

##### Eye contact

If in eyes: Flush eyes with water or saline water (20-30 °C) for at least 5 minutes. Remove contact lenses. Seek medical assistance and continue flushing during transport.

##### Ingestion

If the person is conscious, rinse the mouth with water and stay with the person. Never give the person anything to drink.

In case of malaise, seek medical advice immediately and bring the safety data sheet or label from the product. Do not induce vomiting, unless recommended by the doctor. Have the person lean forward with head down to avoid inhalation of or choking on vomited material.

##### Burns

Not applicable.

#### 4.2. ▼ Most important symptoms and effects, both acute and delayed

Sensitisation: This product contains substances, which may trigger allergic reaction upon dermal contact.

Manifestation of allergic reactions typically takes place within 12-72 hours after exposure.

#### 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

#### Information to medics

Bring this safety data sheet or the label from this product.

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

Suitable extinguishing media: Alcohol-resistant foam, carbon dioxide, powder, water mist.

Unsuitable extinguishing media: Waterjets should not be used, since they can spread the fire.

#### 5.2. Special hazards arising from the substance or mixture

Fire will result in dense smoke. Exposure to combustion products may harm your health. Closed containers, which are exposed to fire, should be cooled with water. Do not allow fire-extinguishing water to enter the sewage system and nearby surface waters.

#### 5.3. Advice for firefighters

Fire fighters should wear appropriate personal protective equipment.

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation, especially in confined areas.

Contaminated areas may be slippery.

#### 6.2. Environmental precautions

Avoid discharge to lakes, streams, sewers, etc.

Keep unauthorized persons away from the spill

**6.3. Methods and material for containment and cleaning up**

Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations.

Wherever possible cleaning should be performed with normal cleaning agents. Avoid use of solvents.

**6.4. Reference to other sections**

See section 13 "Disposal considerations" on handling of waste.

See section 8 "Exposure controls/personal protection" for protective measures.

**SECTION 7: Handling and storage**

**7.1. Precautions for safe handling**

Smoking, drinking and consumption of food is not allowed in the work area.

See section 8 "Exposure controls/personal protection" for information on personal protection.

**7.2. Conditions for safe storage, including any incompatibilities**

Containers that have been opened must be carefully resealed and kept upright to prevent leakage.

**Recommended storage material**

Keep only in original packaging.

**Storage temperature**

No specific requirements

**Incompatible materials**

Strong acids, strong bases, strong oxidizing agents, and strong reducing agents.

**7.3. Specific end use(s)**

This product should only be used for applications quoted in section 1.2.

**SECTION 8: Exposure controls/personal protection**

**8.1. Control parameters**

titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter ≤ 10 µm]

Long term exposure limit (8 hours) (mg/m<sup>3</sup>): 10(inhalable)/4(respirable)

Limestone

Long term exposure limit (8 hours) (mg/m<sup>3</sup>): 10(inhalable)/4(respirable)

2-aminoethanol;ethanolamine

Long term exposure limit (8 hours) (ppm): 1

Long term exposure limit (8 hours) (mg/m<sup>3</sup>): 2,5

Short term exposure limit (15 minutes) (ppm): 3

Short term exposure limit (15 minutes) (mg/m<sup>3</sup>): 7,6

Annotations:

Sk = Can be absorbed through the skin and lead to systemic toxicity.

Tetrasodium pyrophosphate

Long term exposure limit (8 hours) (mg/m<sup>3</sup>): 5

The Control of Substances Hazardous to Health Regulations 2002. SI 2002/2677 The Stationery Office 2002.

EH40/2005 Workplace exposure limits (Fourth Edition 2020).

**DNEL**

1,2-benzisothiazol-3(2H)-one;1,2-benzisothiazolin-3-one

<b>Duration:</b>	<b>Route of exposure:</b>	<b>DNEL:</b>
Long term – Systemic effects - General population	Dermal	345 µg/kgbw/day
Long term – Systemic effects - Workers	Dermal	966 µg/kgbw/day
Long term – Systemic effects - General population	Inhalation	1.2 mg/m <sup>3</sup>
Long term – Systemic effects - Workers	Inhalation	6.81 mg/m <sup>3</sup>

2-aminoethanol;ethanolamine

<b>Duration:</b>	<b>Route of exposure:</b>	<b>DNEL:</b>
------------------	---------------------------	--------------

Long term – Systemic effects - General population	Dermal	1.5 mg/kg bw/day
Long term – Systemic effects - Workers	Dermal	3 mg/kg bw/day
Long term – Local effects - General population	Inhalation	280 µg/m <sup>3</sup>
Long term – Local effects - Workers	Inhalation	510 µg/m <sup>3</sup>
Long term – Systemic effects - General population	Inhalation	180 µg/m <sup>3</sup>
Long term – Systemic effects - Workers	Inhalation	1 mg/m <sup>3</sup>
Long term – Systemic effects - General population	Oral	1.5 mg/kg bw/day

**Tetrasodium pyrophosphate**

<b>Duration:</b>	<b>Route of exposure:</b>	<b>DNEL:</b>
Long term – Systemic effects - General population	Inhalation	4.35 mg/m <sup>3</sup>
Long term – Systemic effects - Workers	Inhalation	17.63 mg/m <sup>3</sup>

titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter ≤ 10 µm]

<b>Duration:</b>	<b>Route of exposure:</b>	<b>DNEL:</b>
Long term – Local effects - General population	Inhalation	28 µg/m <sup>3</sup>
Long term – Local effects - Workers	Inhalation	170 µg/m <sup>3</sup>

**PNEC**

1,2-benzisothiazol-3(2H)-one;1,2-benzisothiazolin-3-one

<b>Route of exposure:</b>	<b>Duration of Exposure:</b>	<b>PNEC:</b>
Freshwater		4.03 µg/L
Freshwater sediment		49.9 µg/kg
Intermittent release (freshwater)		1.1 µg/L
Intermittent release (marine water)		110 ng/L
Marine water		403 ng/L
Marine water sediment		4.99 µg/kg
Sewage treatment plant		1.03 mg/L
Soil		3 mg/kg

**2-aminoethanol;ethanolamine**

<b>Route of exposure:</b>	<b>Duration of Exposure:</b>	<b>PNEC:</b>
Freshwater		70 µg/L
Freshwater sediment		357 µg/kg
Intermittent release (freshwater)		28 µg/L
Marine water		7 µg/L
Marine water sediment		35.7 µg/kg
Sewage treatment plant		100 mg/L
Soil		1.29 mg/kg

**Tetrasodium pyrophosphate**

<b>Route of exposure:</b>	<b>Duration of Exposure:</b>	<b>PNEC:</b>
Freshwater		50 µg/L
Intermittent release (freshwater)		500 µg/L
Marine water		5 µg/L
Sewage treatment plant		50 mg/L

**8.2. Exposure controls**

Compliance with the given occupational exposure limits values should be controlled on a regular basis.

**General recommendations**

Smoking, drinking and consumption of food is not allowed in the work area.

**Exposure scenarios**

There are no exposure scenarios implemented for this product.

**Exposure limits**

Professional users are subjected to the legally set maximum concentrations for occupational exposure. See occupational hygiene limit values above.

**Appropriate technical measures**

The formation of vapours must be kept at a minimum and below current limit values (see above). Installation of a local exhaust system if normal air flow in the work room is not sufficient is recommended. Ensure eyewash and emergency showers are clearly marked.

Apply standard precautions during use of the product. Avoid inhalation of vapours.

**Hygiene measures**

In between use of the product and at the end of the working day all exposed areas of the body must be washed thoroughly. Pay special attention to hands, forearms and face.

**Measures to avoid environmental exposure**

No specific requirements.

**Individual protection measures, such as personal protective equipment**

▼ **Generally**

Use only UKCA marked protective equipment.

**Respiratory Equipment**

No specific requirements

**Skin protection**

No specific requirements.

▼ **Hand protection**

Material	Glove thickness (mm)	Breakthrough time (min.)	Standards
Nitrile	2,0	> 480	EN374-2, EN374-3, EN388, EN407



**Eye protection**

No specific requirements.

**SECTION 9: Physical and chemical properties**

**9.1. Information on basic physical and chemical properties**

**Physical state**

Liquid

**Colour**

Testing not relevant or not possible due to the nature of the product.

**Odour / Odour threshold**

Testing not relevant or not possible due to the nature of the product.

**pH**

Testing not relevant or not possible due to the nature of the product.

**Density (g/cm<sup>3</sup>)**

Testing not relevant or not possible due to the nature of the product.

**Kinematic viscosity**

Testing not relevant or not possible due to the nature of the product.

**Particle characteristics**

Does not apply to liquids.

**Phase changes**

**Melting point/Freezing point (°C)**

Testing not relevant or not possible due to the nature of the product.

**Softening point/range (waxes and pastes) (°C)**

Does not apply to liquids.

**Boiling point (°C)**

Testing not relevant or not possible due to the nature of the product.

**Vapour pressure**

Testing not relevant or not possible due to the nature of the product.

**Relative vapour density**

Testing not relevant or not possible due to the nature of the product.

**Decomposition temperature (°C)**

Testing not relevant or not possible due to the nature of the product.

**Data on fire and explosion hazards**

**Flash point (°C)**

Testing not relevant or not possible due to the nature of the product.

**Flammability (°C)**

Testing not relevant or not possible due to the nature of the product.

**Auto-ignition temperature (°C)**

Testing not relevant or not possible due to the nature of the product.

**Lower and upper explosion limit (% v/v)**

Testing not relevant or not possible due to the nature of the product.

**Solubility**

**Solubility in water**

Testing not relevant or not possible due to the nature of the product.

**n-octanol/water coefficient (LogKow)**

Testing not relevant or not possible due to the nature of the product.

**Solubility in fat (g/L)**

Testing not relevant or not possible due to the nature of the product.

**9.2. Other information**

**Oxidizing properties**

Testing not relevant or not possible due to the nature of the product.

**Other physical and chemical parameters**

No data available.

## SECTION 10: Stability and reactivity

**10.1. Reactivity**

No data available.

**10.2. Chemical stability**

The product is stable under the conditions, noted in section 7 "Handling and storage".

**10.3. Possibility of hazardous reactions**

None known.

**10.4. Conditions to avoid**

None known.

**10.5. Incompatible materials**

Strong acids, strong bases, strong oxidizing agents, and strong reducing agents.

**10.6. Hazardous decomposition products**

The product is not degraded when used as specified in section 1.

## SECTION 11: Toxicological information

**11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008 as retained and amended in UK law**

**Acute toxicity**

Based on available data, the classification criteria are not met.

**Skin corrosion/irritation**

Based on available data, the classification criteria are not met.

**Serious eye damage/irritation**

Based on available data, the classification criteria are not met.

**Respiratory sensitisation**

Based on available data, the classification criteria are not met.

▼ **Skin sensitisation**

This product contains substances that may trigger an allergic reaction in already sensitized persons.

**Germ cell mutagenicity**

Based on available data, the classification criteria are not met.

**Carcinogenicity**

Based on available data, the classification criteria are not met.

**Reproductive toxicity**

Based on available data, the classification criteria are not met.

**STOT-single exposure**

Based on available data, the classification criteria are not met.

**STOT-repeated exposure**

Based on available data, the classification criteria are not met.

**Aspiration hazard**

Based on available data, the classification criteria are not met.

**11.2. Information on other hazards**

**Long term effects**

None known.

**Endocrine disrupting properties**

This mixture/product does not contain any substances known to have hormone-disrupting properties in relation to health.

**Other information**

titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter ≤ 10 µm] has been classified by IARC as a group 2B carcinogen.

**SECTION 12: Ecological information**

**12.1. Toxicity**

No data available.

**12.2. Persistence and degradability**

Based on available data, the classification criteria are not met.

**12.3. Bioaccumulative potential**

Based on available data, the classification criteria are not met.

**12.4. Mobility in soil**

No data available.

**12.5. Results of PBT and vPvB assessment**

This mixture/product does not contain any substances known to fulfil the criteria for PBT and vPvB classification.

**12.6. Endocrine disrupting properties**

This mixture/product does not contain any substances considered to have endocrine-disrupting properties in relation to the environment.

**12.7. Other adverse effects**

None known.

**SECTION 13: Disposal considerations**

**Waste treatment methods**

Product is not covered by regulations on dangerous waste.

Regulation (EU) No 1357/2014 of 18 December 2014 on waste as retained and amended in UK law.

**EWC code**

Not applicable.

**Specific labelling**

**Contaminated packing**

Packaging containing residues of the product must be disposed of similarly to the product.

**SECTION 14: Transport information**

	<b>14.1</b>	<b>14.2</b>	<b>14.3</b>	<b>14.4</b>	<b>14.5</b>	<b>Other</b>
	<b>UN / ID</b>	<b>UN proper shipping name</b>	<b>Hazard class(es)</b>	<b>PG*</b>	<b>Env**</b>	<b>information:</b>
ADR	-	-	-	-	-	-
IMDG	-	-	-	-	-	-
IATA	-	-	-	-	-	-

\* Packing group

\*\* Environmental hazards



**Additional information**

Not dangerous goods according to ADR, IATA and IMDG.

**14.6. Special precautions for user**

Not applicable.

**14.7. Maritime transport in bulk according to IMO instruments**

No data available.

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****Restrictions for application**

No special.

**Demands for specific education**

No specific requirements.

**SEVESO - Categories / dangerous substances**

Not applicable.

**Additional information**

Not applicable.

**Sources**

Regulation (EU) No 1357/2014 of 18 December 2014 on waste as retained and amended in UK law.

Regulation (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures (CLP) as retained and amended in UK law.

Regulation (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) as retained and amended in UK law.

**15.2. Chemical safety assessment**

No

**SECTION 16: Other information****▼ Full text of H-phrases as mentioned in section 3**

H301, Corrosive to the respiratory tract.

H302, Toxic if swallowed.

H310, Harmful if swallowed.

H312, Fatal in contact with skin.

H314, Harmful in contact with skin.

H314, Causes severe skin burns and eye damage.

H315, Causes skin irritation.

H317, May cause an allergic skin reaction.

H318, Causes serious eye damage.

H319, Causes serious eye irritation.

H330, Fatal if inhaled.

H332, Harmful if inhaled.

H335, May cause respiratory irritation.

H400, Very toxic to aquatic life.

H410, Very toxic to aquatic life with long lasting effects.

H412, Harmful to aquatic life with long lasting effects.

**The full text of identified uses as mentioned in section 1**

LCS "C" = Consumer uses: Private households (= general public = consumers)

PROC 10 = Roller application or brushing

PC 9a = Coatings and Paints, Fillers, Putties, Thinners

**Abbreviations and acronyms**

ADN = European Provisions concerning the International Carriage of Dangerous Goods by Inland Waterway

ADR = The European Agreement concerning the International Carriage of Dangerous Goods by Road

ATE = Acute Toxicity Estimate

BCF = Bioconcentration Factor

CAS = Chemical Abstracts Service

CE = Conformité Européenne (European conformity)

CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]

CSA = Chemical Safety Assessment

CSR = Chemical Safety Report

DMEL = Derived Minimal Effect Level  
DNEL = Derived No Effect Level  
EINECS = European Inventory of Existing Commercial chemical Substances  
ES = Exposure Scenario  
EUH statement = CLP-specific Hazard statement  
EuPCS = European Product Categorisation System  
EWC = European Waste Catalogue  
GHS = Globally Harmonized System of Classification and Labelling of Chemicals  
GWP = Global warming potential  
IARC = International Agency for Research on Cancer (IARC)  
IATA = International Air Transport Association  
IBC = Intermediate Bulk Container  
IMDG = International Maritime Dangerous Goods  
LogPow = logarithm of the octanol/water partition coefficient  
MARPOL = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)  
OECD = Organisation for Economic Co-operation and Development  
PBT = Persistent, Bioaccumulative and Toxic  
PNEC = Predicted No Effect Concentration  
RID = The Regulations concerning the International Carriage of Dangerous Goods by Rail  
RRN = REACH Registration Number  
SCL = A specific concentration limit  
SVHC = Substances of Very High Concern  
STOT-RE = Specific Target Organ Toxicity - Repeated Exposure  
STOT-SE = Specific Target Organ Toxicity - Single Exposure  
TWA = Time weighted average  
UN = United Nations  
UVBC = Unknown or variable composition, complex reaction products or of biological materials  
VOC = Volatile Organic Compound  
vPvB = Very Persistent and Very Bioaccumulative

**Additional information**

Not applicable.

▼ **The safety data sheet is validated by**

ST

▼ **Other**

A change (in proportion to the last essential change (first cipher in SDS version, see section 1)) is marked with a triangle.

The information in this safety data sheet applies only to this specific product (mentioned in section 1) and is not necessarily correct for use with other chemicals/products.

It is recommended to hand over this safety data sheet to the actual user of the product. Information in this safety data sheet cannot be used as a product specification.

Country-language: GB-en