



SITOP PSU4200/1AC/24VDC/20A

SITOP PSU4200 1AC 24 V/20 A stabilized power supply PSU4200 input: 120/240 V AC output: 24 V DC/20 A

General information	
Technical Product Detail Page	https://i.siemens.com/1P6EP3336-3SB00-0AX0
input	
type of the power supply network	1-phase AC
supply voltage at AC	
• minimum rated value	120 V
• maximum rated value	240 V
• initial value	85 V
• full-scale value	264 V
wide range input	Yes
buffering time for rated value of the output current in the event of power failure minimum	15 ms
operating condition of the mains buffering	at $V_{in} = 120/240$ V
line frequency	50/60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 100 V	5.4 A
• at rated input voltage 120 V	4.5 A
• at rated input voltage 200 V	2.6 A
• at rated input voltage 230 V	2.4 A
• at rated input voltage 240 V	2.3 A
current limitation of inrush current at 25 °C maximum	20 A
duration of inrush current limiting at 25 °C	
• typical	40 ms
I ² t value maximum	3 A ² ·s
fuse protection type	6.3 A
fuse protection type in the feeder	Recommended miniature circuit breaker: from 10 A characteristic C to from 16 A characteristic C
output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
output voltage adjustable	Yes; via potentiometer
adjustable output voltage	24 ... 28 V
relative overall tolerance of the voltage	3 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.1 %
• on slow fluctuation of ohm loading	1 %

residual ripple	
• maximum	150 mV
• typical	35 mV
voltage peak	
• maximum	240 mV
• typical	67 mV
display version for normal operation	Green LED for 24 V OK
type of signal at output	Signal contact (signal load capacity: 10 mA) for DC OK
behavior of the output voltage when switching on	No overshoot of Vout (soft start)
response delay maximum	1.5 s
voltage increase time of the output voltage	
• typical	33 ms
• maximum	500 ms
output current	
• rated value	20 A
• rated range	0 ... 20 A; +60 ... +70 °C: Derating 3%/K
supplied active power typical	480 W
bridging of equipment	Yes
number of parallel-switched equipment resources for increasing the power	2
efficiency	
efficiency in percent	93 %
power loss [W]	
• at rated output voltage for rated value of the output current typical	37 W
• during no-load operation maximum	3 W
closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	0.2 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	2 %
relative control precision of the output voltage at load step of resistive load 10/90/10 % typical	3 %
setting time	
• load step 10 to 90% typical	1 ms
• load step 90 to 10% typical	1 ms
protection and monitoring	
design of the overvoltage protection	< 32 V
property of the output short-circuit proof	Yes
design of short-circuit protection	Shutdown and periodic restart attempts
• typical	23.1 A
enduring short circuit current RMS value	
• typical	6 A
safety	
galvanic isolation between input and output	Yes
galvanic isolation	Output voltage: SELV, ES1 (IEC 62368-1), DVC As (IEC 61204-7)
operating resource protection class	Class I
leakage current	
• maximum	0.7 mA
• typical	0.5 mA
protection class IP	IP20
EMC	
standard	
• for emitted interference	EN 55032 Class A
• for mains harmonics limitation	EN 61000-3-2
• for interference immunity	EN 61000-6-2
standards, specifications, approvals	
certificate of suitability	
• CE marking	Yes
• UL approval	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259

<ul style="list-style-type: none"> • UKCA marking 	Yes
<ul style="list-style-type: none"> • EAC approval 	Yes
<ul style="list-style-type: none"> • Regulatory Compliance Mark (RCM) 	Yes
<ul style="list-style-type: none"> • NEC Class 2 	No
type of certification	
<ul style="list-style-type: none"> • BIS 	Yes; R-41282421
<ul style="list-style-type: none"> • CB-certificate 	Yes
MTBF at 40 °C	1 065 000 h
standards, specifications, approvals hazardous environments	
certificate of suitability	
<ul style="list-style-type: none"> • IECEx 	No
<ul style="list-style-type: none"> • ATEX 	No
<ul style="list-style-type: none"> • ULhazloc approval 	No
<ul style="list-style-type: none"> • FM registration 	No
standards, specifications, approvals marine classification	
shipbuilding approval	No
Marine classification association	
<ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) 	No
<ul style="list-style-type: none"> • French marine classification society (BV) 	No
<ul style="list-style-type: none"> • Det Norske Veritas (DNV) 	No
<ul style="list-style-type: none"> • Lloyds Register of Shipping (LRS) 	No
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
<ul style="list-style-type: none"> • total 	1 078.9 kg
<ul style="list-style-type: none"> • during manufacturing 	47.4 kg
<ul style="list-style-type: none"> • during operation 	1 029.9 kg
<ul style="list-style-type: none"> • after end of life 	0.72 kg
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> • during operation 	-25 ... +70 °C; with natural convection
<ul style="list-style-type: none"> • during transport 	-40 ... +85 °C
<ul style="list-style-type: none"> • during storage 	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection	push-in terminals
<ul style="list-style-type: none"> • at input 	L, N, PE: push-in for 0.5 ... 4 mm ²
<ul style="list-style-type: none"> • at output 	+, -: push-in for 0.5 ... 6 mm ²
<ul style="list-style-type: none"> • for signaling contact 	13, 14: push-in for 0.2 ... 1.5 mm ²
mechanical data	
width × height × depth of the enclosure	70 × 135 × 125 mm
installation width × mounting height	70 mm × 225 mm
required spacing	
<ul style="list-style-type: none"> • top 	45 mm
<ul style="list-style-type: none"> • bottom 	45 mm
<ul style="list-style-type: none"> • left 	0 mm
<ul style="list-style-type: none"> • right 	0 mm
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
<ul style="list-style-type: none"> • DIN-rail mounting 	Yes
<ul style="list-style-type: none"> • S7 rail mounting 	No
<ul style="list-style-type: none"> • wall mounting 	No
housing can be lined up	Yes
net weight	0.93 kg
further information internet links	
internet link	
<ul style="list-style-type: none"> • to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool 	https://www.siemens.com/tstcloud
<ul style="list-style-type: none"> • to web page: power supplies 	https://siemens.com/sitop

- to website: CAx-Download-Manager
- to website: Industry Online Support

<https://siemens.com/cax>

<https://support.industry.siemens.com>

additional information

other information

Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

security information

security information

Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Classifications

	Version	Classification
eClass	14	27-04-07-01
eClass	12	27-04-07-01
eClass	9.1	27-04-07-01
eClass	9	27-04-07-01
eClass	8	27-04-90-02
eClass	7.1	27-04-90-02
eClass	6	27-04-90-02
ETIM	10	EC002540
ETIM	9	EC002540
ETIM	8	EC002540
ETIM	7	EC002540
IDEA	4	4130
UNSPSC	15	39-12-10-04

Approvals Certificates

Environmental Product Declaration

- global warming potential [CO2 eq] / during manufacturing 47.4 kg
- global warming potential [CO2 eq] / during operation 1029.9 kg
- global warming potential [CO2 eq] / after end of life 0.72 kg
- global warming potential [CO2 eq] / total 1078.9 kg

Environment

General Product Approval



[Manufacturer Declaration](#)

[China RoHS](#)



General Product Approval



[BIS CRS](#)

last modified:

5/5/2026

