

# SAFETY DATA SHEET

## Shesto Limited - Spraycraft Instant Spray Cleaner 150ml Aerosol SP9120

### SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

#### 1.1. Product identifier

**Product name** Shesto Limited - Spraycraft Instant Spray Cleaner 150ml Aerosol SP9120  
**Product No.** 781/1067

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

**Identified uses** Cleaner

#### 1.3. Details of the supplier of the safety data sheet

**Supplier** Shesto Limited  
3 Century Court  
Tolpits Lane  
Watford  
WD18 9RS  
Tel: +44 (0) 20 8451 6188 (Hours 9.00 to 17.00)  
Fax: +44 (0) 20 8451 5450  
Email: sales@shesto.co.uk

#### 1.4. Emergency telephone number

(+44) 02084 516188 (Hours 09:00 - 17:00 Mon to Fri)

### SECTION 2: HAZARDS IDENTIFICATION

#### 2.1. Classification of the substance or mixture

**Classification (1999/45/EEC)** Xn;R20/21. Xi;R36/38. F+;R12.

##### Human health

In high concentrations, vapours and spray mists are narcotic and may cause headache, fatigue, dizziness and nausea.

##### Environment

The product is not expected to be hazardous to the environment.

##### Physical and Chemical Hazards

Pressurised container: Must not be exposed to temperatures above 50°C. The product is extremely flammable, and explosive vapour/air mixtures may be formed even at normal room temperatures.

#### 2.2. Label elements

**Contains** XYLENE

##### Labelling



Harmful



Extremely flammable

##### Risk Phrases

R12	Extremely flammable.
R20/21	Harmful by inhalation and in contact with skin.
R36/38	Irritating to eyes and skin.

##### Safety Phrases

A1	Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.
A2	Do not spray on a naked flame or any incandescent material.
S2	Keep out of the reach of children.
S16	Keep away from sources of ignition - No smoking.
S23	Do not breathe vapour/spray.
S24/25	Avoid contact with skin and eyes.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S36/37	Wear suitable protective clothing and gloves.
S51	Use only in well-ventilated areas.

# Shesto Limited - Spraycraft Instant Spray Cleaner 150ml Aerosol SP9120

## 2.3. Other hazards

This product does not contain any PBT or vPvB substances.

## SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

### 3.2. Mixtures

<b>ACETONE</b>		<b>30-60%</b>
<b>CAS-No.: 67-64-1</b>	<b>EC No.: 200-662-2</b>	<b>Registration Number: 01-2119471330-XX</b>
Classification (EC 1272/2008) Flam. Liq. 2 - H225 EUH066 Eye Irrit. 2 - H319 STOT SE 3 - H336	Classification (67/548/EEC) F;R11 Xi;R36 R66 R67	
<b>PETROLEUM GASES, LIQUEFIELD</b>		<b>10-30%</b>
<b>CAS-No.: 68476-85-7</b>	<b>EC No.: 270-704-2</b>	
Classification (EC 1272/2008) Flam. Gas 1 - H220 Press. Gas, Compressed - H280	Classification (67/548/EEC) F+;R12.	
<b>XYLENE</b>		<b>30-60%</b>
<b>CAS-No.: 1330-20-7</b>	<b>EC No.: 215-535-7</b>	<b>Registration Number: 01-2119488216-XX</b>
Classification (EC 1272/2008) Flam. Liq. 3 - H226 Acute Tox. 4 - H312 Acute Tox. 4 - H332 Skin Irrit. 2 - H315	Classification (67/548/EEC) R10 Xn;R20/21 Xi;R38	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

## SECTION 4: FIRST AID MEASURES

### 4.1. Description of first aid measures

#### General information

Move the exposed person to fresh air at once.

#### Inhalation

Move the exposed person to fresh air at once. Perform artificial respiration if breathing has stopped. Keep the affected person warm and at rest. Get prompt medical attention.

#### Ingestion

Immediately rinse mouth and provide fresh air. Do not induce vomiting. Get medical attention.

#### Skin contact

Wash skin with soap and water. Get medical attention if any discomfort continues.

#### Eye contact

Immediately rinse with water. Continue to rinse for at least 15 minutes. Make sure to remove any contact lenses from the eyes before rinsing. Get medical attention promptly if symptoms occur after washing.

### 4.2. Most important symptoms and effects, both acute and delayed

#### General information

No data available

### 4.3. Indication of any immediate medical attention and special treatment needed

No data available

# Shesto Limited - Spraycraft Instant Spray Cleaner 150ml Aerosol SP9120

## SECTION 5: FIREFIGHTING MEASURES

### 5.1. Extinguishing media

#### Extinguishing media

Water spray, foam, dry powder or carbon dioxide.

### 5.2. Special hazards arising from the substance or mixture

#### Unusual Fire & Explosion Hazards

Extremely flammable. Forms explosive mixtures with air. May explode in a fire. Vapours are heavier than air and may spread near ground to sources of ignition.

#### Specific hazards

Pressurised container: Must not be exposed to temperatures above 50°C.

### 5.3. Advice for firefighters

#### Special Fire Fighting Procedures

Use water spray to reduce vapours. Aerosol cans may explode in a fire. Cool aerosol containers exposed to heat with water spray and remove container, if no risk is involved.

## SECTION 6: ACCIDENTAL RELEASE MEASURES

### 6.1. Personal precautions, protective equipment and emergency procedures

Ensure suitable personal protection (including respiratory protection) during removal of spillages in a confined area.

### 6.2. Environmental precautions

Avoid discharge into drains.

### 6.3. Methods and material for containment and cleaning up

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Absorb in vermiculite, dry sand or earth and place into containers. Provide ventilation and confine spill. Do not allow runoff to sewer.

### 6.4. Reference to other sections

See sections: 7, 8, 11, 12 and 13

## SECTION 7: HANDLING AND STORAGE

### 7.1. Precautions for safe handling

Keep away from heat, sparks and open flame. Read and follow manufacturer's recommendations. Avoid inhalation of vapours and spray mists. Do not spray on a naked flame or any incandescent material. When sprayed on a naked flame or any incandescent material the aerosol vapours can be ignited.

### 7.2. Conditions for safe storage, including any incompatibilities

Extremely flammable. Store at moderate temperatures in dry, well ventilated area. Keep away from heat, sparks and open flame. Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.

### 7.3. Specific end use(s)

No data available

## SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

### 8.1. Control parameters

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
ACETONE	WEL	500 ppm	1210 mg/m <sup>3</sup>	1500 ppm	3620 mg/m <sup>3</sup>	
PETROLEUM GASES, LIQUEFIELD	WEL	1000 ppm	1750 mg/m <sup>3</sup>	1250 ppm	2180 mg/m <sup>3</sup>	
XYLENE	WEL	50 ppm	220 mg/m <sup>3</sup>	100 ppm	441 mg/m <sup>3</sup>	Sk

WEL = Workplace Exposure Limit.

Sk = Can be absorbed through skin.

### 8.2. Exposure controls

#### Respiratory equipment

No specific recommendation made, but respiratory protection must be used if the general level exceeds the recommended occupational exposure limit. In case of inadequate ventilation use suitable respirator.

# Shesto Limited - Spraycraft Instant Spray Cleaner 150ml Aerosol SP9120

## Hand protection

For prolonged or repeated skin contact use suitable protective gloves.

## Eye protection

Wear approved chemical safety goggles where eye exposure is reasonably probable.

## Hygiene measures

When using do not eat, drink or smoke. Wash promptly if skin becomes wet or contaminated.

## SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

### 9.1. Information on basic physical and chemical properties

Appearance	Aerosol.
Colour	Clear
Odour	of solvents
Solubility	Slightly soluble in water.
Initial boiling point and boiling range	-41 (-41 TO 138)
Relative density	0.77
Vapour density (air=1)	Not available
Vapour pressure	Not available
Evaporation rate	Not available
pH-Value, Conc. Solution	Not available
Viscosity	Not available
Decomposition temperature (°C)	Not available
Odour Threshold, Lower	Not available
Odour Threshold, Upper	Not available
Flash point	-40
Auto Ignition Temperature (°C)	465
Flammability Limit - Lower(%)	0.8
Flammability Limit - Upper(%)	13
Partition Coefficient (N-Octanol/Water)	Not available
Oxidising properties	Not available

### 9.2. Other information

Not known.

## SECTION 10: STABILITY AND REACTIVITY

### 10.1. Reactivity

No data available

### 10.2. Chemical stability

Highly volatile.

### 10.3. Possibility of hazardous reactions

Not available.

### 10.4. Conditions to avoid

Avoid heat, flames and other sources of ignition. Avoid exposure to high temperatures or direct sunlight.

### 10.5. Incompatible materials

#### Materials To Avoid

No data available

### 10.6. Hazardous decomposition products

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

## SECTION 11: TOXICOLOGICAL INFORMATION

### 11.1. Information on toxicological effects

#### Inhalation

Harmful by inhalation.

# Shesto Limited - Spraycraft Instant Spray Cleaner 150ml Aerosol SP9120

## Skin contact

Harmful in contact with skin. Irritating to skin.

## Eye contact

Irritating to eyes.

## Health Warnings

In high concentrations, vapours are narcotic and may cause headache, fatigue, dizziness and nausea. Arrhythmia, (deviation from normal heart beat).

## Route of entry

Inhalation. Skin absorption.

## Target Organs

Central nervous system Respiratory system, lungs

## Medical Symptoms

Narcotic effect. Vapours may cause drowsiness and dizziness.

### Toxicological information on ingredients.

#### XYLENE (CAS: 1330-20-7)

##### Acute toxicity:

##### **Acute Toxicity (Oral LD50)**

> 2000 mg/kg

##### **Acute Toxicity (Inhalation LC50)**

> 10 mg/l (vapours)

#### ACETONE (CAS: 67-64-1)

##### Acute toxicity:

##### **Acute Toxicity (Oral LD50)**

5800 mg/kg Rat

##### **Acute Toxicity (Dermal LD50)**

7800 mg/kg Rabbit

##### **Acute Toxicity (Inhalation LC50)**

> 20 mg/l (vapours) Rat

#### PETROLEUM GASES, LIQUEFIELD (CAS: 68476-85-7)

##### Acute toxicity:

##### **Acute Toxicity (Inhalation LC50)**

> 20 mg/l (vapours) Rat 4 hours

## SECTION 12: ECOLOGICAL INFORMATION

### Ecotoxicity

The product is not expected to be toxic to aquatic organisms.

### 12.1. Toxicity

# Shesto Limited - Spraycraft Instant Spray Cleaner 150ml Aerosol SP9120

## Ecological information on ingredients.

### XYLENE (CAS: 1330-20-7)

#### Acute Toxicity - Fish

LC50 > 1<10 mg/l

#### Acute Toxicity - Aquatic Plants

EC50 >1 - <10mg/l (Algae)

### ACETONE (CAS: 67-64-1)

#### Acute Toxicity - Fish

LC50 >100 mg/l (fish)

EC 50, 48 Hrs, Daphnia, mg/l

8800

## 12.2. Persistence and degradability

### Degradability

No data available.

## 12.3. Bioaccumulative potential

### Bioaccumulative potential

No data available on bioaccumulation.

Partition coefficient Not available

## 12.4. Mobility in soil

### Mobility:

No data available

## 12.5. Results of PBT and vPvB assessment

No data available

## 12.6. Other adverse effects

Not available.

## SECTION 13: DISPOSAL CONSIDERATIONS

### 13.1. Waste treatment methods

Make sure containers are empty before discarding (explosion risk). Do not puncture or incinerate even when empty. Dispose of waste and residues in accordance with local authority requirements.

## SECTION 14: TRANSPORT INFORMATION

### 14.1. UN number

UN No. (ADR/RID/ADN) 1950

UN No. (IMDG) 1950

UN No. (ICAO) 1950

### 14.2. UN proper shipping name

Proper Shipping Name AEROSOLS

### 14.3. Transport hazard class(es)

ADR/RID/ADN Class 2

ADR/RID/ADN Class Class 2: Gases

ADR Label No. 2.1

IMDG Class 2.1

ICAO Class/Division 2.1

ICAO Subsidiary risk 2.1

Transport Labels

# Shesto Limited - Spraycraft Instant Spray Cleaner 150ml Aerosol SP9120



## 14.4. Packing group

ADR/RID/ADN Packing group N/A

ICAO Packing group N/A

## 14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant

No.

## 14.6. Special precautions for user

EMS F-D, S-U

Tunnel Restriction Code (D)

## 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not relevant

## SECTION 15: REGULATORY INFORMATION

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### Uk Regulatory References

Health and Safety at Work Act 1974. Chemicals (Hazard Information & Packaging) Regulations. The Control of Substances Hazardous to Health Regulations 2002 (S.I 2002 No. 2677) with amendments.

#### Statutory Instruments

Control of Substances Hazardous to Health.

#### Approved Code Of Practice

Safety Data Sheets for Substances and Preparations. Classification and Labelling of Substances and Preparations Dangerous for Supply.

#### EU Legislation

Dangerous Preparations Directive 1999/45/EC.

### 15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out.

## SECTION 16: OTHER INFORMATION

Revision Date 21/01/2013

Revision 3

Supersedes date 23/05/2006

#### Risk Phrases In Full

R12	Extremely flammable.
R10	Flammable.
R20/21	Harmful by inhalation and in contact with skin.
R11	Highly flammable
R36/38	Irritating to eyes and skin.
R36	Irritating to eyes.
R38	Irritating to skin.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

# Shesto Limited - Spraycraft Instant Spray Cleaner 150ml Aerosol SP9120

## Hazard Statements In Full

H319	Causes serious eye irritation.
H315	Causes skin irritation.
H280	Contains gas under pressure; may explode if heated.
H222	Extremely flammable aerosol.
H220	Extremely flammable gas.
H226	Flammable liquid and vapour.
H332	Harmful if inhaled.
H312	Harmful in contact with skin.
H225	Highly flammable liquid and vapour.
H336	May cause drowsiness or dizziness.
EUH066	Repeated exposure may cause skin dryness or cracking.

## Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.