

UT 1,5 BU - Feed-through terminal block



1452264

<https://www.phoenixcontact.com/de/produkte/1452264>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 1000 V, nominal current: 17.5 A, number of connections: 2, connection method: Screw connection, Rated cross section: 1.5 mm², cross section: 0.14 mm² - 1.5 mm², mounting type: NS 35/7,5, NS 35/15, color: blue

Your advantages

- The large wiring space enables the connection of solid and stranded conductors without ferrules, even above the nominal cross section
- As well as saving space, the compact design enables user-friendly wiring in a small amount of space
- Optimum screwdriver guidance through closed screw shafts
- Tested for railway applications
- The cable entry funnel enables the use of conductors with ferrules and plastic collars within the nominal cross section

Commercial data

Item number	1452264
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	A1 - Reihenklemmen
Product key	BE1111
GTIN	4063151840242
Weight per piece (including packing)	5,769 g
Weight per piece (excluding packing)	22,22 g
Customs tariff number	85369010
Country of origin	IN

UT 1,5 BU - Feed-through terminal block



1452264

<https://www.phoenixcontact.com/de/produkte/1452264>

Technical data

Product properties

Product type	Feed-through terminal block
Area of application	Railway industry
	Machine building
	Plant engineering
	Process industry
Number of connections	2
Number of rows	1
Potentials	1

Data management status

Article revision	00
------------------	----

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	0.56 W

Connection data

Number of connections per level	2
Nominal cross section	1.5 mm ²
Rated cross section AWG	16
Screw thread	M2
Tightening torque	0.22 ... 0.25 Nm
Stripping length	7 mm ... 8 mm
Internal cylindrical gage	A1
	B1
Conductor cross section rigid	0.14 mm ² ... 1.5 mm ²
Cross section AWG	26 ... 16 (converted acc. to IEC)
Conductor cross section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross section, flexible [AWG]	26 ... 16 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.14 mm ² ... 1 mm ²
Flexible conductor cross section (ferrule with plastic sleeve)	0.14 mm ² ... 0.75 mm ²
2 conductors with same cross section, solid	0.14 mm ² ... 0.75 mm ²
2 conductors with same cross section, flexible	0.14 mm ² ... 0.75 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.14 mm ² ... 0.34 mm ²
Nominal current	17.5 A
Maximum load current	17.5 A (with 1.5 mm ² conductor cross section)
Nominal voltage	1000 V

UT 1,5 BU - Feed-through terminal block



1452264

<https://www.phoenixcontact.com/de/produkte/1452264>

Nominal cross section	1.5 mm ²
-----------------------	---------------------

Dimensions

Width	4.15 mm
Height	48 mm
Depth	46.9 mm

Material specifications

Color	blue
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, no longer than 24 h, -60°C to +70°C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 35/7,5
	NS 35/15

UT 1,5 BU - Feed-through terminal block


1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



Drawings

Circuit diagram



UT 1,5 BU - Feed-through terminal block



1452264

<https://www.phoenixcontact.com/de/produkte/1452264>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/de/produkte/1452264>

 cCSAus Approval ID: 13631				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Use group B	600 V	15 A	30 - 14	-
Use group C	600 V	15 A	30 - 14	-
Use group F	1000 V	15 A	30 - 14	-
Use group D	600 V	5 A	30 - 14	-

 cULus Recognized Approval ID: E60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Use group B	600 V	15 A	30 - 14	-
Use group C	600 V	15 A	30 - 14	-
Use group F	1000 V	15 A	30 - 14	-
Use group D	600 V	5 A	30 - 14	-

DNV Approval ID: TAE00001S9				
---------------------------------------	--	--	--	--

UT 1,5 BU - Feed-through terminal block



1452264

<https://www.phoenixcontact.com/de/produkte/1452264>

Classifications

ECLASS

ECLASS-11.0	27141120
ECLASS-13.0	27250101

ETIM

ETIM 8.0	EC000897
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UT 1,5 BU - Feed-through terminal block



1452264

<https://www.phoenixcontact.com/de/produkte/1452264>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



Accessories

i Note: Applying some accessories below might limit this product.

FBS 2-4 - Plug-in bridge

3030116

<https://www.phoenixcontact.com/de/produkte/3030116>



Plug-in bridge, pitch: 4.2 mm, number of positions: 2, color: red

i Max. current carrying capacity: 17.5 A

FBS 3-4 - Plug-in bridge

3030129

<https://www.phoenixcontact.com/de/produkte/3030129>



Plug-in bridge, pitch: 4.2 mm, number of positions: 3, color: red

i Max. current carrying capacity: 17.5 A

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



FBS 4-4 - Plug-in bridge

3030132

<https://www.phoenixcontact.com/de/produkte/3030132>



Plug-in bridge, pitch: 4.2 mm, number of positions: 4, color: red

 Max. current carrying capacity: 17.5 A

FBS 5-4 - Plug-in bridge

3030145

<https://www.phoenixcontact.com/de/produkte/3030145>



Plug-in bridge, pitch: 4.2 mm, number of positions: 5, color: red

 Max. current carrying capacity: 17.5 A

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



FBS 10-4 - Plug-in bridge

3030158

<https://www.phoenixcontact.com/de/produkte/3030158>



Plug-in bridge, pitch: 4.2 mm, number of positions: 10, color: red

 Max. current carrying capacity: 17.5 A

FBS 20-4 - Plug-in bridge

3030352

<https://www.phoenixcontact.com/de/produkte/3030352>



Plug-in bridge, pitch: 4.2 mm, number of positions: 20, color: red

 Max. current carrying capacity: 17.5 A

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



FBS 2-4 BU - Plug-in bridge

3030117

<https://www.phoenixcontact.com/de/produkte/3030117>



Plug-in bridge, pitch: 4.2 mm, number of positions: 2, color: blue

 Max. current carrying capacity: 17.5 A

FBS 3-4 BU - Plug-in bridge

3030130

<https://www.phoenixcontact.com/de/produkte/3030130>



Plug-in bridge, pitch: 4.2 mm, number of positions: 3, color: blue

 Max. current carrying capacity: 17.5 A

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



FBS 4-4 BU - Plug-in bridge

3030133

<https://www.phoenixcontact.com/de/produkte/3030133>



Plug-in bridge, pitch: 4.2 mm, number of positions: 4, color: blue

 Max. current carrying capacity: 17.5 A

FBS 5-4 BU - Plug-in bridge

3030146

<https://www.phoenixcontact.com/de/produkte/3030146>



Plug-in bridge, pitch: 4.2 mm, number of positions: 5, color: blue

 Max. current carrying capacity: 17.5 A

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



FBS 10-4 BU - Plug-in bridge

3036851

<https://www.phoenixcontact.com/de/produkte/3036851>



Plug-in bridge, pitch: 4.2 mm, number of positions: 10, color: blue

 Max. current carrying capacity: 17.5 A

FBS 20-4 BU - Plug-in bridge

3030353

<https://www.phoenixcontact.com/de/produkte/3030353>



Plug-in bridge, pitch: 4.2 mm, number of positions: 20, color: blue

 Max. current carrying capacity: 17.5 A

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



FBS 2-4 GY - Plug-in bridge

3030118

<https://www.phoenixcontact.com/de/produkte/3030118>



Plug-in bridge, pitch: 4.2 mm, number of positions: 2, color: gray

 Max. current carrying capacity: 17.5 A

FBS 3-4 GY - Plug-in bridge

3030131

<https://www.phoenixcontact.com/de/produkte/3030131>



Plug-in bridge, pitch: 4.2 mm, number of positions: 3, color: gray

 Max. current carrying capacity: 17.5 A

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



FBS 4-4 GY - Plug-in bridge

3030134

<https://www.phoenixcontact.com/de/produkte/3030134>



Plug-in bridge, pitch: 4.2 mm, number of positions: 4, color: gray

 Max. current carrying capacity: 17.5 A

FBS 5-4 GY - Plug-in bridge

3030147

<https://www.phoenixcontact.com/de/produkte/3030147>



Plug-in bridge, pitch: 4.2 mm, number of positions: 5, color: gray

 Max. current carrying capacity: 17.5 A

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



D-UT 2,5/10 - End cover

3047028

<https://www.phoenixcontact.com/de/produkte/3047028>

End cover, depth: 39.8 mm, width: 2.2 mm, height: 47 mm, color: gray



ATP-UT - Partition plate

3047167

<https://www.phoenixcontact.com/de/produkte/3047167>

Partition plate, depth: 45.7 mm, width: 2.2 mm, height: 53.4 mm, color: gray



UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



NS 35/ 7,5 PERF 2000MM - DIN rail perforated

0801733

<https://www.phoenixcontact.com/de/produkte/0801733>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

NS 35/ 7,5 UNPERF 2000MM - DIN rail, unperforated

0801681

<https://www.phoenixcontact.com/de/produkte/0801681>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



NS 35/ 7,5 WH PERF 2000MM - DIN rail perforated

1204119

<https://www.phoenixcontact.com/de/produkte/1204119>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

NS 35/ 7,5 WH UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1204122

<https://www.phoenixcontact.com/de/produkte/1204122>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



NS 35/ 7,5 AL UNPERF 2000MM - DIN rail, unperforated

0801704

<https://www.phoenixcontact.com/de/produkte/0801704>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver

NS 35/ 7,5 ZN PERF 2000MM - DIN rail perforated

1206421

<https://www.phoenixcontact.com/de/produkte/1206421>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, Standard profile, color: silver

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



NS 35/ 7,5 ZN UNPERF 2000MM - DIN rail, unperforated

1206434

<https://www.phoenixcontact.com/de/produkte/1206434>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, Standard profile, color: silver

NS 35/ 7,5 CU UNPERF 2000MM-VPE 10 - DIN rail, unperforated

0801762

<https://www.phoenixcontact.com/de/produkte/0801762>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



NS 35/ 7,5 CAP - End cap

1206560

<https://www.phoenixcontact.com/de/produkte/1206560>

DIN rail end piece, for DIN rail NS 35/7.5



NS 35/15 PERF 2000MM - DIN rail perforated

1201730

<https://www.phoenixcontact.com/de/produkte/1201730>



DIN rail perforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



NS 35/15 UNPERF 2000MM - DIN rail, unperforated

1201714

<https://www.phoenixcontact.com/de/produkte/1201714>



DIN rail, unperforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

NS 35/15 WH PERF 2000MM - DIN rail perforated

0806602

<https://www.phoenixcontact.com/de/produkte/0806602>



DIN rail perforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: white

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



NS 35/15 WH UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1204135

<https://www.phoenixcontact.com/de/produkte/1204135>



DIN rail, unperforated, Pack of 10 (20 m), similar to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

NS 35/15 AL UNPERF 2000MM - DIN rail, unperforated

1201756

<https://www.phoenixcontact.com/de/produkte/1201756>



DIN rail, unperforated, similar to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



NS 35/15 ZN PERF 2000MM - DIN rail perforated

1206599

<https://www.phoenixcontact.com/de/produkte/1206599>



DIN rail perforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, Standard profile, color: silver

NS 35/15 ZN UNPERF 2000MM - DIN rail, unperforated

1206586

<https://www.phoenixcontact.com/de/produkte/1206586>



DIN rail, unperforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, Standard profile, color: silver

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



NS 35/15 CU UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1201895

<https://www.phoenixcontact.com/de/produkte/1201895>



DIN rail, unperforated, Pack of 10 (20 m), similar to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored

NS 35/15 CAP - End cap

1206573

<https://www.phoenixcontact.com/de/produkte/1206573>

DIN rail end piece, for DIN rail NS 35/15



UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



NS 35/15-2,3 UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1201798

<https://www.phoenixcontact.com/de/produkte/1201798>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile 2.3 mm, color: silver

ZB 4 :UNBEDRUCKT - Zack marker strip

0805001

<https://www.phoenixcontact.com/de/produkte/0805001>



Zack marker strip, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 4.2 mm, lettering field size: 4.2 x 10.5 mm, Number of individual labels: 10

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



ZB 4 CUS - Zack marker strip

0824951

<https://www.phoenixcontact.com/de/produkte/0824951>



Zack marker strip, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 4.2 mm, lettering field size: 4.2 x 10.5 mm, Number of individual labels: 10

ZB 4,LGS:FORTL.ZAHLEN - Zack marker strip

0805739

<https://www.phoenixcontact.com/de/produkte/0805739>



Zack marker strip, Strip, white, labeled, printed horizontally: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: snapped, for terminal block width: 4.2 mm, lettering field size: 4.2 x 10.5 mm, Number of individual labels: 10

UT 1,5 BU - Feed-through terminal block

1452264


<https://www.phoenixcontact.com/de/produkte/1452264>



ZB 4,QR:FORTL.ZAHLEN - Zack marker strip

0805807

<https://www.phoenixcontact.com/de/produkte/0805807>



Zack marker strip, Strip, white, labeled, Printed vertically: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: snapped, for terminal block width: 4.2 mm, lettering field size: 4.2 x 10.5 mm, Number of individual labels: 10

UC-TM 4 - Marker for terminal blocks

0818111

<https://www.phoenixcontact.com/de/produkte/0818111>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 4.2 mm, lettering field size: 3.6 x 10.5 mm, Number of individual labels: 120

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



UC-TM 4 CUS - Marker for terminal blocks

0824573

<https://www.phoenixcontact.com/de/produkte/0824573>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 4.2 mm, lettering field size: 3.6 x 10.5 mm, Number of individual labels: 120

UCT-TM 4 - Marker for terminal blocks

0828732

<https://www.phoenixcontact.com/de/produkte/0828732>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped, for terminal block width: 4.2 mm, lettering field size: 3.6 x 10.5 mm, Number of individual labels: 84

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



UCT-TM 4 CUS - Marker for terminal blocks

0829588

<https://www.phoenixcontact.com/de/produkte/0829588>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 4.2 mm, lettering field size: 3.6 x 10.5 mm, Number of individual labels: 84

STP 4-2-ZB - Marker carriers

3038613

<https://www.phoenixcontact.com/de/produkte/3038613>



Marker carriers, snaps into ST 1,5... spring-cage terminal blocks, can be marked with UC-TM 4, UC-TMF 4, UCT-TM 4, UCT-TMF 4, ZB 4, or ZBF 4, gray, unlabeled, mounting type: snapped, lettering field size: 4 x 10.5 mm

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



ZBF 4:UNBEDRUCKT - Zack Marker strip, flat

0808587

<https://www.phoenixcontact.com/de/produkte/0808587>



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: snapped, for terminal block width: 4 mm, lettering field size: 4.2 x 5.2 mm, Number of individual labels: 10

ZBF 4 CUS - Zack Marker strip, flat

0825023

<https://www.phoenixcontact.com/de/produkte/0825023>



Zack Marker strip, flat, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 4.2 mm, lettering field size: 4.2 x 5.2 mm, Number of individual labels: 10

UT 1,5 BU - Feed-through terminal block



1452264

<https://www.phoenixcontact.com/de/produkte/1452264>

ZBF 4,LGS:FORTL.ZAHLEN - Zack Marker strip, flat

0808626

<https://www.phoenixcontact.com/de/produkte/0808626>



Zack Marker strip, flat, Strip, white, labeled, printed horizontally: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: snapped, for terminal block width: 4 mm, lettering field size: 4.2 x 5.2 mm, Number of individual labels: 10

ZBF 4,QR:FORTL.ZAHLEN - Zack Marker strip, flat

0808820

<https://www.phoenixcontact.com/de/produkte/0808820>



Zack Marker strip, flat, Strip, white, labeled, Printed vertically: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: snapped, for terminal block width: 4 mm, lettering field size: 4.2 x 5.2 mm, Number of individual labels: 10

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



ZBF 4,LGS:GERADE ZAHLEN - Zack Marker strip, flat

0810818

<https://www.phoenixcontact.com/de/produkte/0810818>



Zack Marker strip, flat, Strip, white, labeled, printed horizontally: consecutive even numbers 2 ... 20, 22 ... 40, etc. up to 82 ... 100, mounting type: snapped, for terminal block width: 4 mm, lettering field size: 5.15 x 4.15 mm, Number of individual labels: 10

ZBF 4,LGS:UNGERADE ZAHLEN - Zack Marker strip, flat

0810850

<https://www.phoenixcontact.com/de/produkte/0810850>



Zack Marker strip, flat, Strip, white, labeled, printed horizontally: Odd numbers 1 - 19, 21 - 39, etc. up to 81 - 99, mounting type: snapped, for terminal block width: 4 mm, lettering field size: 5.15 x 4.15 mm, Number of individual labels: 10

UT 1,5 BU - Feed-through terminal block




1452264

<https://www.phoenixcontact.com/de/produkte/1452264>

UC-TMF 4 - Marker for terminal blocks

0818166

<https://www.phoenixcontact.com/de/produkte/0818166>




Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 4.2 mm, lettering field size: 3.6 x 5.1 mm, Number of individual labels: 120

UC-TMF 4 CUS - Marker for terminal blocks

0824630

<https://www.phoenixcontact.com/de/produkte/0824630>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 4.2 mm, lettering field size: 3.6 x 5.1 mm, Number of individual labels: 120

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



UCT-TMF 4 - Marker for terminal blocks

0828742

<https://www.phoenixcontact.com/de/produkte/0828742>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped, for terminal block width: 4.2 mm, lettering field size: 3.4 x 4.7 mm, Number of individual labels: 90

UCT-TMF 4 CUS - Marker for terminal blocks

0829651

<https://www.phoenixcontact.com/de/produkte/0829651>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 4.2 mm, lettering field size: 3.4 x 4.7 mm, Number of individual labels: 90

UT 1,5 BU - Feed-through terminal block



1452264

<https://www.phoenixcontact.com/de/produkte/1452264>

PAI-4 - Test adapter

3030925

<https://www.phoenixcontact.com/de/produkte/3030925>



Test adapter, Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in, for 4 mm test plug and terminal blocks with 8.2 mm pitch, number of positions: 1, color: gray

PS-4 - Test plug

3030970

<https://www.phoenixcontact.com/de/produkte/3030970>



Test plug, Modular test plug, number of positions: 1, color: red

UT 1,5 BU - Feed-through terminal block

1452264

<https://www.phoenixcontact.com/de/produkte/1452264>



DP PS-4 - Spacer plate

3036712

<https://www.phoenixcontact.com/de/produkte/3036712>



Spacer plate, depth: 29 mm, width: 4.2 mm, height: 22.4 mm, number of positions: 1, color: red

SZF 0-0,4X2,5 - Screwdriver

1204504

<https://www.phoenixcontact.com/de/produkte/1204504>



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.4 x 2.5 x 75 mm, 2-component grip, with non-slip grip

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstraße 8
D-32825 Blomberg
+49 52 35/3-1 20 00
info@phoenixcontact.de