

VAL-SPP-T2-1000DC-PV-2+V-UT - Type 2 surge arrester



1466772

<https://www.phoenixcontact.com/de/produkte/1466772>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge arrester, in accordance with type 2/Class II, for 2-pos. insulated and grounded 1000 V DC PV systems, for DIN rail mounting, 3-pos. base element, three pluggable temperature-monitored protective elements, status message on each plug.

Your advantages

- Easy and safe installation with forward-thinking handling and safety features
- Reliable system protection with maximum performance and endurance
- Can be used in a wide range of applications due to the optimized design and broad portfolio
- Simple planning due to comprehensive digital data and selectors

Commercial data

Item number	1466772
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	K1 - Überspannungsschutz
Product key	CL13A2
GTIN	4063151862466
Weight per piece (including packing)	327,1 g
Weight per piece (excluding packing)	299,2 g
Customs tariff number	85363010
Country of origin	DE

VAL-SPP-T2-1000DC-PV-2+V-UT - Type 2 surge arrester



1466772
<https://www.phoenixcontact.com/de/produkte/1466772>

Technical data

Product properties

Product type	PV arrester
IEC test classification	PV II
	PV T2
EN type	T2
IEC power supply system	DC
Type	DIN rail module, two-section, divisible
Number of positions	3
Installation location	Interior
Installation location of the disconnect device	Internal
Accessibility	Accessible
Connection configuration	Y configuration
SPD failure behavior	OCFM (Open-Circuit Failure Mode)
Surge protection fault message	optical

Data management status

Article revision	02
------------------	----

Insulation characteristics

Overvoltage category	III
Pollution degree	2

Connection data

Connection method	Screw connection
Screw thread	M5
Tightening torque	2.5 Nm ... 3 Nm
Stripping length	12 mm
Conductor cross section flexible	1.5 mm² ... 16 mm²
	2x 1.5 mm² ... 6 mm² (2 conductors with the same cross-section)
Conductor cross section rigid	1.5 mm² ... 25 mm²
	2x 1.5 mm² ... 6 mm² (2 conductors with the same cross-section)
Conductor cross section AWG	15 ... 4
Conductor cross section, flexible, with ferrule, with plastic sleeve	1.5 mm² ... 16 mm²
	2x 1.5 mm² ... 6 mm² (2 conductors with the same cross-section)
Conductor cross section flexible, with ferrule without plastic sleeve	1.5 mm² ... 16 mm²
	2x 1.5 mm² ... 6 mm² (2 conductors with the same cross-section)

Dimensions

Dimensional drawing	
---------------------	--

VAL-SPP-T2-1000DC-PV-2+V-UT - Type 2 surge arrester



1466772

<https://www.phoenixcontact.com/de/produkte/1466772>

Width	53.4 mm
Height	96.6 mm
Depth	71.5 mm (incl. DIN rail 7.5 mm)
Horizontal pitch	3 Div.

Material specifications

Color	gray (RAL 7042)
	light gray (RAL 7035)
Flammability rating according to UL 94	V-0
CTI value of material	600
Insulating material	PA 6.6-FR 20 % GF
	PBT
Material group	I
Housing material	PA 6.6-FR 20 % GF
	PBT

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Protective circuit

Mode of protection	(DC+) - (DC-)
	(DC+) - PE
	(DC-) - PE
Residual current I_{PE}	$\leq 350 \mu A$ AC
	$\leq 100 \mu A$ DC
Standby power consumption P_C	≤ 120.00 mVA
Nominal discharge current I_n (8/20) μs	20 kA
Maximum discharge current I_{max} (8/20) μs	40 kA
Total discharge current I_{total} (8/20) μs	40 kA
Voltage protection level U_p	≤ 4.2 kV
Residual voltage U_{res}	≤ 4.2 kV (at I_n)
	≤ 3.6 kV (at 10 kA)
	≤ 3.2 kV (at 5 kA)
	≤ 3 kV (at 3 kA)
Response time t_A	≤ 25 ns

PV protective circuit

Connection configuration	Y configuration
SPD failure behavior	OCFM (Open-Circuit Failure Mode)

Protective circuit DC voltage side (DC)

Open circuit voltage U_{OCSTC}	1000 V DC
Maximum discharge current I_{max} (8/20) μs	40 kA
Response time t_A	≤ 25 ns

VAL-SPP-T2-1000DC-PV-2+V-UT - Type 2 surge arrester



1466772

<https://www.phoenixcontact.com/de/produkte/1466772>

Total discharge current I_{total} (8/20) μs	40 kA
Insulation resistance R_{iso}	> 5 M Ω (at 500 V DC)
Nominal discharge current I_n (8/20) μs	20 kA
Continuous operating current I_{CPV}	$\leq 100 \mu\text{A DC}$
Maximum continuous operating voltage U_{CPV}	1200 V DC
Short-circuit current rating I_{SCPV}	15000 A
Residual voltage U_{res}	$\leq 4.2 \text{ kV}$ (at I_n)
	$\leq 3.6 \text{ kV}$ (at 10 kA)
	$\leq 3.2 \text{ kV}$ (at 5 kA)
	$\leq 3 \text{ kV}$ (at 3 kA)
Residual current I_{pE}	$\leq 350 \mu\text{A AC}$
	$\leq 100 \mu\text{A DC}$
Voltage protection level U_p	$\leq 4.2 \text{ kV}$
Standby power consumption P_C	$\leq 120.00 \text{ mVA}$

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20C (Installed)
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Altitude	$\leq 5000 \text{ m}$ (amsl)
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	25g (Half-sine / 11 ms / 3x $\pm X$, $\pm Y$, $\pm Z$)
Vibration (operation)	5g (5-500 Hz/2.5 h/XYZ)

Standards and regulations

Standards/specifications	EN 61643-31
Note	2019
Standards/specifications	IEC 61643-31
Note	2018

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------


VAL-SPP-T2-1000DC-PV-2+V-UT - Type 2 surge arrester

1466772

<https://www.phoenixcontact.com/de/produkte/1466772>

Drawings

Dimensional drawing




VAL-SPP-T2-1000DC-PV-2+V-UT - Type 2 surge arrester

1466772

<https://www.phoenixcontact.com/de/produkte/1466772>

Circuit diagram



VAL-SPP-T2-1000DC-PV-2+V-UT - Type 2 surge arrester



1466772

<https://www.phoenixcontact.com/de/produkte/1466772>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/de/produkte/1466772>



IECEE CB Scheme

Approval ID: NL-109183

CCA

Approval ID: NTR NL-8030



KEMA-KEUR

Approval ID: 71-133324

VAL-SPP-T2-1000DC-PV-2+V-UT - Type 2 surge arrester



1466772
<https://www.phoenixcontact.com/de/produkte/1466772>

Classifications

ECLASS

ECLASS-11.0	27130805
ECLASS-13.0	27171402

VAL-SPP-T2-1000DC-PV-2+V-UT - Type 2 surge arrester



1466772
<https://www.phoenixcontact.com/de/produkte/1466772>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

VAL-SPP-T2-1000DC-PV-2+V-UT - Type 2 surge arrester



1466772

<https://www.phoenixcontact.com/de/produkte/1466772>

Accessories

VAL-SPP-T2-1000DC-PV-P - Type 2 surge protection plug

1466779

<https://www.phoenixcontact.com/de/produkte/1466779>




Replacement plug for PV special combined lightning current and surge arrester from the VAL-SPP-T2-1000DC-PV-2+V-UT... product family.

VAL-SPP-BE-2+V/PV-UT - Surge protection base-element

1466785

<https://www.phoenixcontact.com/de/produkte/1466785>



Base element for surge arresters, for insulated DC voltage systems, for DIN rail mounting, 3-pos. base element without remote indication contact.

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Deutschland GmbH

Flachmarktstraße 8

D-32825 Blomberg

+49 52 35/3-1 20 00

info@phoenixcontact.de