

# Termination block - PTPOWER 95-3L - 3260109

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Termination block, Connection method: Push-in connection, Number of positions: 3, Cross section: 25 mm<sup>2</sup> - 95 mm<sup>2</sup>, AWG: 4 - 3/0, Width: 75 mm, Color: gray, Mounting type: NS 35/15

## Product Features

- Quick and easy connection is now also possible for large conductors with the high-current terminal block
- The push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- The compact design and front connection enable wiring in a confined space
- In addition to the testing facility in the double function shaft, all terminal blocks provide an additional test connection

## Key commercial data

package_quantity	3
GTIN	4046356778756

## Technical data

### General

Number of levels	1
Number of connections	2
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

### General

Maximum load current	232 A (with 95 mm <sup>2</sup> conductor cross section)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I <sub>N</sub>	232 A
Nominal voltage U <sub>N</sub>	1500 V
Open side panel	nein
Number of positions	3

### Dimensions

Width	75 mm
-------	-------

# Termination block - PTPOWER 95-3L - 3260109

## Technical data

### Dimensions

<b>Length</b>	105.5 mm
<b>Height NS 35/15</b>	108.7 mm

### Connection data

<b>Conductor cross section solid min.</b>	25 mm <sup>2</sup>
<b>Conductor cross section solid max.</b>	95 mm <sup>2</sup>
<b>Conductor cross section AWG/kcmil min.</b>	4
<b>Conductor cross section AWG/kcmil max</b>	3/0
<b>Conductor cross section stranded min.</b>	25 mm <sup>2</sup>
<b>Conductor cross section stranded max.</b>	95 mm <sup>2</sup>
<b>Min. AWG conductor cross section, stranded</b>	4
<b>Max. AWG conductor cross section, stranded</b>	4/0
<b>Conductor cross section stranded, with ferrule without plastic sleeve min.</b>	25 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule without plastic sleeve max.</b>	95 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule with plastic sleeve min.</b>	25 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule with plastic sleeve max.</b>	95 mm <sup>2</sup>
<b>Cross section with insertion bridge, solid max.</b>	95 mm <sup>2</sup>
<b>Cross section with insertion bridge, stranded max.</b>	70 mm <sup>2</sup>
<b>Connection method</b>	Push-in connection
<b>Stripping length</b>	40 mm

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27141120
<b>eCl@ss 4.1</b>	27141120
<b>eCl@ss 5.0</b>	27141120
<b>eCl@ss 5.1</b>	27141120
<b>eCl@ss 6.0</b>	27141120
<b>eCl@ss 7.0</b>	27141120
<b>eCl@ss 8.0</b>	27141120

### ETIM

<b>ETIM 3.0</b>	EC000897
<b>ETIM 4.0</b>	EC000897
<b>ETIM 5.0</b>	EC000897

### UNSPSC

<b>UNSPSC 6.01</b>	30211811
<b>UNSPSC 7.0901</b>	39121410
<b>UNSPSC 11</b>	39121410

# Termination block - PTPOWER 95-3L - 3260109

## classifications

### UNSPSC

UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

## approvals

---

GOST /

---

### Approval details



## accessories

### Pick-off terminal block

AGK 10-PTPOWER - 3260145



AGK 10-PTPOWER BU - 3260148



AGK 10-PTPOWER GN/YE - 3260151



# Termination block - PTPOWER 95-3L - 3260109

## accessories

AGK 10-PTPOWER BK/YE - 3260154



---

## Screwdriver tools

SZF 3-1,0X5,5 - 1206612



---

## Documentation

PT-IL - 3208090



---

## Bridge

EB 2-25/PT - 3260157



EB 3-25/PT - 3260160



# Termination block - PTPOWER 95-3L - 3260109

accessories

## Mounting rail

NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



## Termination block - PTPOWER 95-3L - 3260109

### accessories

NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



### End block

E/AL-NS 35 - 1201662



### Terminal marking

# Termination block - PTPOWER 95-3L - 3260109

## accessories

TMT (EX9,5)R - 0828295



ZB 16:UNPRINTED - 0827461



UC-TM 16 - 0819217



UCT-TM 16 - 0829146



ZBF 16:UNPRINTED - 0827464



UC-TMF 16 - 0819262



# Termination block - PTPOWER 95-3L - 3260109

accessories

---

UCT-TMF 16 - 0829218



## Labeled terminal marker

ZB 16 CUS - 0827463



UC-TM 16 CUS - 0824621



UCT-TM 16 CUS - 0829637



ZBF 16 CUS - 0827465





## Termination block - PTPOWER 95-3L - 3260109

### accessories

UC-TMF 16 CUS - 0824678



UCT-TMF 16 CUS - 0829693



### Test plug terminal block

MPS-MT - 0201744



### Insulating sleeve

MPS-IH WH - 0201663



MPS-IH RD - 0201676



# Termination block - PTPOWER 95-3L - 3260109

## accessories

MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



## Planning and marking software

# Termination block - PTPOWER 95-3L - 3260109

## accessories

CLIP-PROJECT ADVANCED - 5146040



CLIP-PROJECT PROFESSIONAL - 5146053



## Drawings

Circuit diagram

