

Heat shrinking Tube Service Kit, Transparent

Item No. : 2004CA104



This range is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics and the laboratory needs. Shrinking ration 2:1 standard for a range of application diameter from 2.0 to 16.5 mm. The heat-shrink tubing can be used for insulation, protective covering of components, as anti-kink protection, protection against corrosion, as well as repair of cables and lines, and much more be used.

Shrinking ratio	2 : 1
Material	PE
Shrinking temperature	70°C - 110°C
Operation temperature	-55°C - 110°C
Flammability	VW-1
Tensile strength	≥ 10.3 Mpa
Elongation at break	≥ 300%
Rated voltage	600V
Diselectric strength	≥ 1.5kv/mm at 30sec.
Volume resistivity	≥ 10 ¹⁴ Ω

set contents

Heat shrink tube		Length
Inner diameter ø	after shrink ø	
2.0 mm	0.85 mm	3 m
3.0 mm	1.30 mm	3 m
4.0 mm	1.80 mm	3 m
6.5 mm	3.00 mm	2 m
8.5 mm	4.00 mm	2 m
12.5 mm	6.00 mm	1.5 m
16.5 mm	8.00 mm	1 m