

Set heat-shrink crimp-connectors and heat-shrink tubing (1140 parts) - Type: 2107C407

This set contains a 340-piece premium crimp connector assortment in the shrink ratio 3:1 for an application range for cable cross sections from 0.5 to 6 qmm, the hot-melt inner adhesive closes watertight when overlapped correctly. Optimal for repairing or connecting cables and conductors (lawn mower search cables, signal cables, etc.), service, manufacturing or hobby. Application is very simple: strip cable and insert on both sides until stripped cable ends overlap. Crimp with crimping pliers and then activate the heat shrink tubing in the respective temperature range - ideally with a heat gun.

Also included are premium shrinking tubes with a shrink ratio of 2:1 in various lengths and diameters from 1.5 to 12 mm in an extra assortment box.



Content

- Crimp connector 150 pcs. red Ø 4.7 mm, length 36 mm, 0.5 ... 1,5 qmm, 19 A
- Crimp connector 100 pcs. Blue Ø 5.7 mm, length 37 mm, 1.5 ... 2,5 qmm, 27 A
- Crimp connector 50 pcs. White Ø 4.0 mm, length 26 mm, 0.3 ... 0,5 qmm, 9 A
- Crimp connector 20 pcs. Yellow Ø 6.9 mm, length 42 mm, 4.0 ... 6.0 qmm, 48 A
- Crimp connector 20 pcs. black Ø 6.0 mm, length 38 mm, 2.5 ... 4,0 qmm, 35 A
- Heat shrinkable tubing 300 pieces - Ø 1.5 mm - length - 45 mm, black
- Heat shrinkable tubing 220 pieces - Ø 2,5 mm - length - 45 mm, black
- Heat shrinkable tubing 60 pieces - Ø 3,5 mm - length - 65 mm, Black
- Heat shrinkable tubing 30 pieces - Ø 5 mm - length - 65 mm, Black
- Heat shrinkable tubing 25 pieces - Ø 6 mm - length - 45 mm, Black
- Heat shrinkable tubing 55 pieces - Ø 8 mm - length - 45 mm, Black
- Heat shrinkable tubing 55 pieces - Ø 9 mm - length - 65 mm, Black
- Heat shrinkable tubing 55 pieces - Ø 12 mm - length - 65 mm, Black