




Connectors > Automotive Connectors > Connector Housings



Connector & Housing Type: **Housing for Female Terminals**

Mating Tab Width: **.64 mm [ .025 in ]**

Connector System: **Wire-to-Wire**

Number of Positions: **26**

Centerline (Pitch): **2.54 mm [ .1 in ]**

Features

Product Type Features

Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	No
Hybrid Connector	No

Configuration Features

Number of Positions	26
Number of Rows	2

Body Features

Body Material	Other
Primary Product Color	Black

Contact Features

Mating Tab Width	.64 mm[.025 in]
------------------	-----------------

Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	No
Strain Relief	No

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------



Dimensions

Product Width	7.9 mm[.311 in]
Product Length	33.7 mm[1.323 in]
Product Height	20.4 mm[.803 in]
Row-to-Row Spacing	5.9 mm[.232 in]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Agency/Standard	USCAR-2
UL Flammability Rating	UL 94HB

Packaging Features

Packaging Quantity	50
Packaging Method	Package

Other

Serviceable	No
Connector Position Assurance Capable	No

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

















Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 1326362-1 26WAY LAC "COMMON" SHIELD ASMB</p>	 <p>TE Part # 1326136-2 26WAY LAC "SINGLE GEAR" ASMBLY</p>	 <p>TE Part # 638551-3 CONTACT,FEMALE,0.64MM,SN,18-20</p>	 <p>TE Part # 1326028-3 0.64MM FEMALE CONTACT,AU,18-20</p>
 <p>TE Part # 1326028-5 .64MM FEM CONT,AU,18-20,FORMED</p>	 <p>TE Part # 638551-1 CONTACT,FEMALE,0.64MM,SN,18-20</p>	 <p>TE Part # 1326028-2 0.64MM FEMALE CONTACT,AU, 22AWG</p>	 <p>TE Part # 638551-4 CONTACT,FEMALE,0.64MM,SN,22</p>
 <p>TE Part # 1326028-1 0.64MM FEMALE CONTACT,AU,18-20</p>	 <p>TE Part # 638551-2 CONTACT,FEMALE,0.64MM,SN,22</p>	 <p>TE Part # 1326028-4 0.64MM FEMALE CONTACT,AU, 22AWG</p>	 <p>TE Part # 1326028-6 0.64MM FEMALE CONTACT,AU, 22AWG</p>
 <p>TE Part # 1326122-1 52WAY LAC "SINGLE GEAR" SHIELD</p>	 <p>TE Part # 1326136-1 26WAY LAC "SINGLE GEAR" ASMBLY</p>	 <p>TE Part # 1326362-3 26WAY LAC "COMMON" SHIELD ASMB</p>	 <p>TE Part # 1326362-2 26WAY LAC "COMMON" SHIELD ASMB</p>

Also in the Series | AMP 0.64 Connector System



Automotive Connector Caps & Covers  
(19)

Automotive Headers(44)

Automotive Housings(31)

Automotive Terminals(13)

Insertion & Extraction Tools(1)

Other Automotive Connector  
Accessories(1)

Customers Also Bought

TE Part #1-953892-1  
MQS, CONNECTOR HOUSING

TE Part #1326029-1  
1.5/2.8 CONNECTOR SYSTEM, RECPT  
AND TAB

TE Part #1326362-1  
26WAY LAC "COMMON" SHIELD  
ASMB

TE Part #121397P023  
ES2000-NO.3-B8-0-27MM

TE Part #1326133-1  
RECEPTACLE HOUSING, 18 POSITIO

TE Part #121397P043  
ES2000-NO.3-B8-0-40MM

TE Part #1-2035366-0  
AMPSEAL 16 BACKSHELLS

TE Part #HDP26-24-16PE-L017  
PLG, 16P, BLK, E, RNG, 12, P

Documents

- Product Drawings

LAC CARRIER, 26 POS, 0.64MM, A KEY

English
- CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1326042-1\_S.2d\_dxf.zip



English

Customer View Model

[ENG\\_CVM\\_CVM\\_1326042-1\\_S.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1326042-1\\_S.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Instruction Sheets

Instruction Sheet (U.S.)

English