




Connectors > Automotive Connectors > Connector Housings > TH/.025 CONNECTOR SYSTEM, HOUSING



Connector & Housing Type: **Housing for Male Terminals**

Mating Tab Width: **.64 mm [.025 in]**

Connector System: **Wire-to-Wire**

Number of Positions: **4**

Centerline (Pitch): **2.2 mm [.087 in]**

[All TH/.025 CONNECTOR SYSTEM, HOUSING \(205\)](#)

Features

Product Type Features

Connector & Housing Type	Housing for Male Terminals
Connector System	Wire-to-Wire
Sealable	No
Hybrid Connector	No
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	14 VDC
Nominal Voltage Architecture	12 V

Body Features

Cable Exit Angle	180°
Body Material	PBT
Primary Product Color	Black

Contact Features

Mating Tab Width	.64 mm[.025 in]
------------------	-----------------



Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	Yes
Strain Relief	No
Mating Alignment Type	Polarized

Housing Features

Centerline (Pitch)	2.2 mm[.087 in]
--------------------	-----------------

Dimensions

Product Width	33.4 mm[1.315 in]
Product Length	14 mm[.551 in]
Product Height	11.75 mm[.463 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C [158 °F][167 °F][176 °F][185 °F][194 °F][212 °F]
Operating Temperature Range	-40 – 100 °C[-40 – 212 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM,
HOUSING




TE Part # CAT-T319-T273
TH/.025 CONNECTOR SYSTEM,
RECPT AND TAB


Also in the Series | TH/.025 Connector System




Automotive Connector Caps & Covers
(6)



Automotive Headers(147)



Automotive Housings(206)



Automotive Seals & Cavity Plugs(2)



Automotive Terminals(31)



Insertion & Extraction Tools(4)



Other Automotive Connector Accessories(5)

Customers Also Bought



TE Part #1411169-3
GET .64 CONNECTOR SYSTEM,
CONNECTOR HSG



TE Part #1379659-5
TH/.025 CONNECTOR SYSTEM,
HOUSING



TE Part #1241406-3
AMP MCP, RECEPTACLE AND TAB



TE Part #144617-1
TIMER, RECEPTACLE AND TAB



TE Part #1379101-1
COV+LEV MQS 18W 90DEG BLK



TE Part #1393449-1
V23540A1000Y452=VERSCHL.26P.



TE Part #1379918-1
COVER FOR 20W TAB HSG



TE Part #965383-1
MQS SICHERGSCHIEBER 8POS

Documents

Product Drawings

4W TAB HSG CODING 1 BLACK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1379674-1_A_c-1379674-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1379674-1_A_c-1379674-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1379674-1_A_c-1379674-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

TH/.025 Connector Series

English

Product Specifications

Product Specification

English

Packaging specification for TH Tab en Plug (TH TES)

English

Product Environmental Compliance

MD_1379674-1_031520181236_dmtec

English

MD_1379674-1_031520181236_dmtec

English

Instruction Sheets

Instruction Sheet (non U.S.)

English