

Siemens
EcoTech



SIMATIC S7-1500 Analog input module, AI 8xU/I/R/RTD BA, 16 bit resolution, Accuracy 0.5%, 8 channels in groups of 8; Common mode voltage 4 V DC, Diagnostics; Hardware interrupts; Delivery including infeed element, shield bracket and shield terminal; Front connector (screw terminals or push-in) to be ordered separately

General information

Product type designation	AI 8xU/I/R/RTD BA
HW functional status	FS01
Firmware version	V1.0.0
• FW update possible	Yes

Product function

• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
• Prioritized startup	No
• Measuring range scalable	No
• Scalable measured values	No
• Adjustment of measuring range	No

Engineering with

• STEP 7 TIA Portal configurable/integrated from version	V15.1 / V16
• STEP 7 configurable/integrated from version	V5.5 SP3 / -
• PROFIBUS from GSD version/GSD revision	V1.0 / V5.1
• PROFINET from GSD version/GSD revision	V2.3 / -

Operating mode

• Oversampling	No
• MSI	Yes

CIR - Configuration in RUN

Reparameterization possible in RUN	Yes
Calibration possible in RUN	No

Input current

Current consumption, max.	0 mA
---------------------------	------

Power

Power consumption from the backplane bus	0.85 W
--	--------

Power loss

Power loss, typ.	0.9 W
------------------	-------

Address area

Address space per module	
• Inputs	16 byte
• Outputs	0 byte

Analog inputs

Number of analog inputs	8
• For current measurement	8

• For voltage measurement	8
• For resistance/resistance thermometer measurement	8
permissible input voltage for voltage input (destruction limit), max.	12 V; 12 V continuous, 30 V for max. 1 s
permissible input current for current input (destruction limit), max.	40 mA
Constant measurement current for resistance-type transmitter, typ.	230 ... 370 μ A
Technical unit for temperature measurement adjustable	Yes; °C/°F/K
Analog input with oversampling	No
Standardization of measured values	No
Input ranges (rated values), voltages	
• 0 to +5 V	No
• 0 to +10 V	No
• 1 V to 5 V	Yes
— Input resistance (1 V to 5 V)	10 M Ω
• -1 V to +1 V	Yes
— Input resistance (-1 V to +1 V)	10 M Ω
• -10 V to +10 V	Yes
— Input resistance (-10 V to +10 V)	10 M Ω
• -2.5 V to +2.5 V	No
• -25 mV to +25 mV	No
• -250 mV to +250 mV	No
• -5 V to +5 V	Yes
— Input resistance (-5 V to +5 V)	10 M Ω
• -50 mV to +50 mV	Yes
— Input resistance (-50 mV to +50 mV)	10 M Ω
• -500 mV to +500 mV	Yes
— Input resistance (-500 mV to +500 mV)	10 M Ω
• -80 mV to +80 mV	No
Input ranges (rated values), currents	
• 0 to 20 mA	Yes
— Input resistance (0 to 20 mA)	25 Ω ; Plus approx. 42 ohms for overvoltage protection by PTC
• -20 mA to +20 mA	Yes
— Input resistance (-20 mA to +20 mA)	25 Ω ; Plus approx. 42 ohms for overvoltage protection by PTC
• 4 mA to 20 mA	Yes
— Input resistance (4 mA to 20 mA)	25 Ω ; Plus approx. 42 ohms for overvoltage protection by PTC
Input ranges (rated values), thermocouples	
• Type B	No
• Type C	No
• Type E	No
• Type J	No
• Type K	No
• Type L	No
• Type N	No
• Type R	No
• Type S	No
• Type T	No
• Type U	No
• Type TXK/TXK(L) to GOST	No
Input ranges (rated values), resistance thermometer	
• Cu 10	No
• Cu 10 according to GOST	No
• Cu 50	No
• Cu 50 according to GOST	No
• Cu 100	No
• Cu 100 according to GOST	No
• Ni 10	No
• Ni 10 according to GOST	No
• Ni 100	Yes; Standard/climate

— Input resistance (Ni 100)	10 MΩ
• Ni 100 according to GOST	No
• Ni 1000	Yes; Standard/climate
— Input resistance (Ni 1000)	10 MΩ
• Ni 1000 according to GOST	No
• LG-Ni 1000	Yes; Standard/climate
— Input resistance (LG-Ni 1000)	10 MΩ
• Ni 120	No
• Ni 120 according to GOST	No
• Ni 200	No
• Ni 200 according to GOST	No
• Ni 500	No
• Ni 500 according to GOST	No
• Pt 10	No
• Pt 10 according to GOST	No
• Pt 50	No
• Pt 50 according to GOST	No
• Pt 100	Yes; Standard/climate
— Input resistance (Pt 100)	10 MΩ
• Pt 100 according to GOST	No
• Pt 1000	Yes; Standard/climate
— Input resistance (Pt 1000)	10 MΩ
• Pt 1000 according to GOST	No
• Pt 200	No
• Pt 200 according to GOST	No
• Pt 500	No
• Pt 500 according to GOST	No
Input ranges (rated values), resistors	
• 0 to 150 ohms	No
• 0 to 300 ohms	No
• 0 to 600 ohms	Yes
— Input resistance (0 to 600 ohms)	10 MΩ
• 0 to 3000 ohms	No
• 0 to 6000 ohms	Yes
— Input resistance (0 to 6000 ohms)	10 MΩ
• PTC	Yes
— Input resistance (PTC)	10 MΩ
Cable length	
• shielded, max.	200 m; 50 m at 50 mV
Analog value generation for the inputs	
Measurement principle	integrating
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit
• Integration time, parameterizable	Yes
• Integration time (ms)	2,5 / 16,67 / 20 / 100 ms
• Basic conversion time, including integration time (ms)	10 / 24 / 27 / 107 ms
— additional conversion time for wire-break monitoring	4 ms (to be considered in R/RTD/U 1 to 5 V measurement)
— additional conversion time for resistance measurement	8 ms
• Interference voltage suppression for interference frequency f1 in Hz	400 / 60 / 50 / 10 Hz
Smoothing of measured values	
• Number of smoothing levels	4
• parameterizable	Yes
• Step: None	Yes
• Step: low	Yes
• Step: Medium	Yes
• Step: High	Yes
Encoder	

Connection of signal encoders	
• for voltage measurement	Yes
• for current measurement as 2-wire transducer	Yes; with external supply
• for current measurement as 4-wire transducer	Yes
• for resistance measurement with two-wire connection	Yes; Only for PTC
• for resistance measurement with three-wire connection	Yes; All measuring ranges except PTC; internal compensation of the cable resistances
• for resistance measurement with four-wire connection	No
Errors/accuracies	
Linearity error (relative to input range), (+/-)	0.1 %
Temperature error (relative to input range), (+/-)	0.006 %/K
Crosstalk between the inputs, max.	-50 dB
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.1 %
Operational error limit in overall temperature range	
• Voltage, relative to input range, (+/-)	0.5 %
• Current, relative to input range, (+/-)	0.5 %
• Resistance, relative to input range, (+/-)	0.5 %
• Resistance thermometer, relative to input range, (+/-)	Ptxxx Standard: ± 1.2 K, Ptxxx Climate: ± 0.8 K, Nixxx Standard: ± 0.8 K, Nixxx Climate: ± 0.8 K
Basic error limit (operational limit at 25 °C)	
• Voltage, relative to input range, (+/-)	0.3 %
• Current, relative to input range, (+/-)	0.3 %
• Resistance, relative to input range, (+/-)	0.3 %
• Resistance thermometer, relative to input range, (+/-)	Ptxxx Standard: ± 1.0 K, Ptxxx Climate: ± 0.5 K, Nixxx Standard: ± 0.5 K, Nixxx Climate: ± 0.5 K
Interference voltage suppression for $f = n \times (f_1 \pm 1 \%)$, f_1 = interference frequency	
• Series mode interference (peak value of interference < rated value of input range), min.	40 dB
• Common mode voltage, max.	4 V
• Common mode interference, min.	60 dB
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	
• Diagnostic alarm	Yes
• Limit value alarm	Yes; two upper and two lower limit values in each case
Diagnoses	
• Monitoring the supply voltage	No
• Wire break	Yes; Only for 1 ... 5 V, 4 ... 20 mA, R, and RTD
• Short-circuit	No
• Group error	No
• Overflow/Underflow	Yes
Diagnostics indication LED	
• RUN LED	Yes; green LED
• ERROR LED	Yes; red LED
• MAINT LED	No
• Monitoring of the supply voltage (PWR-LED)	No
• Channel status display	Yes; green LED
• for channel diagnostics	Yes; red LED
• for module diagnostics	Yes; red LED
Potential separation	
Potential separation channels	
• between the channels	No
• between the channels, in groups of	8
• between the channels and backplane bus	Yes
Permissible potential difference	
between the inputs (UCM)	8 V DC
Between the inputs and MANA (UCM)	4 V DC
Isolation	
Isolation tested with	707 V DC (type test)

Standards, approvals, certificates	
Siemens Eco Profile (SEP)	Siemens EcoTech
Suitable for applications according to AMS 2750	No
Suitable for applications according to CQI-9	No
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	38.6 kg
— global warming potential, (during production) [CO2 eq]	14.4 kg
— global warming potential, (during operation) [CO2 eq]	24.6 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.44 kg
Security	
signed firmware update	No
safely removing data	No
data integrity	No
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C; From FS05
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C; From FS05
• vertical installation, max.	40 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
Absolute humidity	
• dew point, min.	-60 °C; suitable for dry room applications
Dimensions	
Width	35 mm
Height	147 mm
Depth	129 mm
Weights	
Weight, approx.	250 g
Classifications	

	Version	Classification
eClass	14	27-24-22-01
eClass	12	27-24-22-01
eClass	9.1	27-24-22-01
eClass	9	27-24-22-01
eClass	8	27-24-22-01
eClass	7.1	27-24-22-01
eClass	6	27-24-22-01
ETIM	10	EC001420
ETIM	9	EC001420
ETIM	8	EC001420
ETIM	7	EC001420
IDEA	4	3562
UNSPSC	15	32-15-17-05

Approvals / Certificates	
General Product Approval	

[Manufacturer Declaration](#)

[Miscellaneous](#)



General Product Approval	For use in hazardous locations
--------------------------	--------------------------------



[China RoHS](#)

[Manufacturer Declaration](#)



[FM](#)

For use in hazardous locations

[CCC-Ex](#)



[Type Examination Certificate](#)

[Miscellaneous](#)

[CCC-Ex](#)

Maritime application



[NK / Nippon Kaiji Kyokai](#)



Maritime application	Environment
----------------------	-------------



[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)



last modified:

5/8/2026